





PIN NO.	NAME	PIN NO.	NAME
C1	VCC	C4	VPP
C2	GND	C5	CLK
C3	RST	C6	IO



NOTES:

1. MATERIAL:

- 1). HOUSING MATERIAL: THERMOPLASTIC UL94V-0; COLOR: BLACK
- 2). CONTACT MATERIAL: COPPER ALLOY, T=0.15mm
- 3). SHELL MATERIAL: STAINLESS STEEL, T=0.15mm

2. FINISH:

- 1). CONTACT FINISH: 50u" MIN. NICKEL UNDER PLATED, PLATED 3u" Au ON CONTACT AREA; PLATED GOLD FLASH ON SOLDER AREA.
- 2). SHELL FINISH: 50u" MIN. NICKEL UNDER PLATED, PLATED GOLD FLASH ON SOLDER AREA.

3. ELECTRICAL SPECIFICATIONS:

- 1). VOLTAGE RATING: 12 VAC
- 2). CURRENT: 1 AMPERES MAX. PER CONTACT
- 3). OPERATION TEMPERATURE RANGE: -25°C ~ +70°C
- 4). CONTACT RESISTANCE: 60M Ω MAX.
- 5). INSULATION RESISTANCE: 1000M Ω MIN.
- 6). DIELECTRIC WITHSTANDING VOLTAGE: 500V AC FOR 1 MINUTE
- 7). MAX. PROCESSING TEMP: 260°C for 30 SECONDS



深圳市华宇创精密电子有限公司

TOLERANCE: X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X.' ±2" X.X' ±0.5" UNIT: mm [inch] SCALE: 1:1 SIZE: A4	DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: MICRO SIM 6P 连桥带档1.6H	
	CHECKED BY: 马跃	DATE : 2014-02-23	PART NO.	HYCW350-SIM06-160B
	APPROVED BY: 邱敏	DATE : 2014-02-23	DRAW NO:	HYC-2312271829
			SHEET NO.	1 OF 1