


TE Internal #: 1-796387-2
24 Position Circular Power Connector, Connector Assembly, 250 VDC, Wire-to-Board / Wire-to-Panel, Receptacle, Pin, Signal, Black, All Plastic, AMP CPC

[View on TE.com >](#)



Connectors > Power Connectors > Circular Power > Circular Power Connectors



Number of Positions: 24
Connector Product Type: Connector Assembly
Operating Voltage: 250 VDC
Connector System: Wire-to-Board, Wire-to-Panel
Sealable: No

Features

Termination Features

Termination Method to PCB	Through Hole - Solder
---------------------------	-----------------------

Packaging Features

Packaging Quantity	8
Packaging Method	Tray

Mechanical Attachment

Panel Mount Feature Type	Flange with Mounting Holes
Mating Alignment Type	Keyed
Mating Retention Type	Threaded Coupling
Mating Alignment	With
Connector Mounting Type	Panel Mount
Mating Retention	With
Panel Mount Feature	With

Configuration Features

Number of Positions	24
---------------------	----



Number of Power Positions	0
Number of Signal Positions	24

Product Type Features

Connector Product Type	Connector Assembly
Connector System	Wire-to-Board, Wire-to-Panel
Sealable	No
Connector & Housing Type	Receptacle
Circular Connector Shell Type	All Plastic

Electrical Characteristics

Operating Voltage	250 VAC
-------------------	---------

Contact Features

Reverse Gender	No
Contact Type	Pin

Housing Features

Housing Color	Black
Housing Material	PA 6.6
Circular Connector Shell Size	23

Dimensions

Assembly Length	61.72 mm[2.43 in]
-----------------	-------------------

Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
Fluid Resistance	None

Operation/Application

Circuit Application	Signal
Shielded	No

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # 207299-4
FLANGE PLUG



TE Part # 796382-2
R/A STRN RELIEF KIT,SZ 23,CPC



TE Part # 6-2407269-3
CAP, CPC, SIZE 23 RECP, RED



TE Part # 6-2407269-4
CAP, CPC, SIZE 23 RECP, YELLOW



TE Part # 206512-6
LARGE CABLE CLAMP KIT,BULK PKG



TE Part # 206837-1
CPC PLUG ASSEMBLY SIZE 23-24




TE Part # 207055-1
EXTENDER BACK SHELL



TE Part # 6-2407269-2
CAP, CPC, SIZE 23 RECP, BLACK





TE Part # 6-2407269-1
CAP, CPC, SIZE 23 RECP, ORANGE



TE Part # 207774-4
CABLE CLAMP ASY,SZ 23,BULK PKG



TE Part # 206138-8
CLAMP CBL SHELL SIZE 23



TE Part # 1-206138-0
CABLE CLAMP ASSY,BULK PACKED



TE Part # 1546350-2
R/A CABLE CLAMP KIT,SZ 23,CPC



TE Part # 206512-5
CLAMP,CABLE SHELL,SIZE 23



TE Part # 206837-2
CPC PLUG,SZ 23-24,SMALL PACK



TE Part # 206837-3
CPC PLUG ASSEMBLY SIZE 23-24



TE Part # 207774-3
CLAMP CABLE SHELL,SIZE 23

Also in the Series | AMP CPC




Circular Connector Backshells & Clamps(1)



Circular Power Connectors(423)



Connector Contacts(6)



Connector Hardware(12)



Power Contacts(6)



Sealing Sleeves(2)

Customers Also Bought



TE Part #205206-8
HDP-20, PLUG, SIZE 2, 15 POSN



TE Part #2-5747704-0
25 PLUG SP/FMS BRDLK



TE Part #2-5748003-0
09 PLUG SP/FMS BRDLK



TE Part #52928
PIDG SPRSPD 22-16COM22-18MIL 5




TE Part #2-5747707-0
15 RCPT SP/FMS BRDLK



TE Part #5747877-3
FEMALE SCREWLOCK ZINC CLEAR



TE Part #1-796406-1
CPC PSTD RCPT, 23-37, R/A LF



TE Part #1-5207908-3
KIT S/R SCREW RET 90/180 DEG



TE Part #1-796409-1
CPC PSTD RCPT, 23-37, R/A LF



TE Part #3-1991253-7
37 WAY LOW COST D SUB BACKSHEL

Documents

CAD Files

3D PDF

English

Customer View Model

ENG_CVM_1-796387-2_C.2d_dxf.zip

English

Customer View Model

ENG_CVM_1-796387-2_C.3d_igs.zip

English

Customer View Model

ENG_CVM_1-796387-2_C.3d_stp.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-796387-2_E.2d_dxf.zip

English

Customer View Model



[ENG_CVM_CVM_1-796387-2_E.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-796387-2_E.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[AMP Circular Connectors for Commercial Signal & Power Applications](#)

English

Product Specifications

[Application Specification](#)

English