






INSPECTION DIMENSION: (A) ~ (M)

SPECIFICATIONS

1. D-SUB

- 1.1 Voltage: 250 VAC(RMS) Max.
- 1.2 Current Rating: 3 Ampere per Contact
- 1.3 Contact Resistance: 25 Milliohms Max.
- 1.4 Insulation Resistance: 5000 Megohms Min.
- 1.5 Dielectric Withstanding Voltage: 1000V AC(RMS)
- 1.6 Total Mating Force: 4.0 Kgf Max.
- 1.7 Total Unmating Force: 1.0 Kgf Min.
- 1.8 Operating Temperature: -55°C to +85°C

2. VGA

- 2.1 Voltage: 250 VAC(RMS) Max.
- 2.2 Current Rating: 3 Ampere per Contact
- 2.3 Contact Resistance: 25 Milliohms Max.
- 2.4 Insulation Resistance: 5000 Megohms Min.
- 2.5 Dielectric Withstanding Voltage: 1000V AC(RMS)
- 2.6 Total Mating Force: 6.0 Kgf Max.
- 2.7 Total Unmating Force: 1.2 Kgf Min.
- 2.8 Operating Temperature: -55°C to +85°C

NOTES

1. MATERIAL:

Housing(UPPER):PA9T, UL 94V-0, Color:Black.
Housing(LOWER):PA9T, UL 94V-0, Color:Black.
Terminal:Copper Alloy.
Shell:SPCC.
Boardlock:Copper Alloy.
Bracket:Zinc Alloy.
Screw:Copper Alloy.

2. FINISH:

Terminal:Gold Plated over Nickel at Contact Area.
Tin Plated over Nickel at Solder Ared.
Shell:Nickel Plated.
Boardlock:Tin Plated.
Bracket:Nickel Plated.
Screw:Nickel Plated.

3. This Product is LEAD-FREE & RoHS Compliance Product.



深圳市华宇创精密电子有限公司

TOLERANCE: X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X' ±2" X.X' ±0.5"	DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: DR9公 对 HDR15母 间距15.88	
	CHECKED BY: 马跃	DATE : 2014-02-23	PART NO.	HYCW172-VGA24C-158B
	APPROVED BY: 邱敏	DATE : 2014-02-23	MOLD NO.	
	UNIT: mm [inch] SCALE:1:1 SIZE: A4		DRAW NO:	HYC-2208131746
			SHEET NO.	1 OF 1