



NANO SIM CARD	
Pin No.	NAME
C1	VCC
C2	RST
C3	CLK
C5	GND
C6	VPP
C7	I/O
S/W	Switch Pin

NOTES:

1. ELECTRICAL CHARACTERISTICS

- 1-1. CONTACT RESISTANCE: 60 Milliohms Max
- 1-2. INSULATION RESISTANCE: 1,000 Megohms Min.
- 1-3. VOLTAGE RATING: 50V.
- 1-4. CURRENT RATING: 1.0A.

2. MECHANICAL CHARACTERISTICS


- 2-1. OPERATION TEMPERATURE RANGE: -20°C~+85°C
- 2-2. DURABILITY: 5000 CYCLES

3. MATERIAL:

- 3-1. HOUSING: THERMOPLASTIC, UL 94-V0
- 3-2. TERMINAL: PHOSPHOR BRONZE, T=0.15
- 3-3. SHELL: STAINLESS STEEL, T=0.20

4. FINISHED:


- 4-1. TERMINAL: Ni PLATED UNDER, 1U" Au MIN PLATED ON CONTACT AREA, AU PLATED ON SOLDER TAIL



STEP 1 INSERT Micro-SIM CARD




STEP 2 PUSH THE SHELL



STEP 3 FINISH

Circuit Diagram for Card Detect Switch



RECOMMENDED PCB LAYOUT

GENERAY TOLERANCE ±0.05

SMT SOLDER AREA



深圳市华宇创精密电子有限公司

TOLERANCE: X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X.' ±2" X.X' ±0.5"	DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: NANO SIM 6P掀盖1.5H 带检测PIN
	CHECKED BY: 马跃	DATE : 2014-02-23	PART NO. HYCW319-SIM07-150B
UNIT: mm [inch] SCALE:1:1 SIZE: A4	APPROVED BY: 邱敏	DATE : 2014-02-23	DRAW NO: HYC-2208061649
			SHEET NO. 1 OF 1