



INSPECTION DIMENSION:(A)~(M)

1. MATERIAL:  
Housing(9P):PBT, UL 94V-0, Color:Green.  
Housing(DVI):PBT, UL 94V-0, Color:Ivory.  
Terminal:Copper Alloy.  
Shell:SPCC.  
Boardlock:Copper Alloy.  
Bracket:Zinc Alloy.  
Screw:Copper Alloy.
2. FINISH:  
Terminal:Gold Plated over Nickel at Contact Area.  
Tin Plated over Nickel at Solder Ared.  
Shell:Nickel Plated.  
Boardlock:Tin Plated.  
Bracket:Nickel Plated.  
Screw:Nickel Plated.
3. This Product is RoHS Compliance Product.

1. VGA
  - 1.1 Voltage: 250 VAC(RMS) Max.
  - 1.2 Current Rating: 3 Ampere per Contact
  - 1.3 Contact Resistance: 25 Milliohms Max.
  - 1.4 Insulation Resistance: 5000 Megohms Min.
  - 1.5 Dielectric Withstanding Voltage: 1000V AC(RMS)
  - 1.6 Total Mating Force: 4.0 Kgf Max.
  - 1.7 Total Unmating Force: 1.0 Kgf Min.
  - 1.8 Operating Temperature: -55°C to +85°C
2. DVI
  - 2.1 Voltage: 50 VAC(RMS) Max.
  - 2.2 Current Rating: 1.5 Ampere per Contact
  - 2.3 Contact Resistance: 20 Milliohms Max.
  - 2.4 Insulation Resistance: 1000 Megohms Min.
  - 2.5 Dielectric Withstanding Voltage: 500V DC(RMS)
  - 2.6 Total Mating Force: 4.5 Kgf Max.
  - 2.7 Total Unmating Force: 1.0 Kgf Min.
  - 2.8 Operating Temperature: -55°C to +85°C



|                                                                                       |          |             |            |                     |                   |
|---------------------------------------------------------------------------------------|----------|-------------|------------|---------------------|-------------------|
| TOLERANCE:                                                                            |          | DRAWN BY :  | DATE :     | PART NAME:          |                   |
| X.X ±0.30                                                                             |          | 陈一鸣         | 2014-02-23 | DR9公+DVI 24+5铆合20.4 |                   |
| X.XX ±0.25                                                                            |          |             |            |                     |                   |
| X.XXX ±0.15                                                                           |          |             |            |                     |                   |
| X: ±2° X.X: ±0.5°                                                                     |          | CHECKED BY: | DATE :     | PART NO.            | HYCW29-DVI38-204B |
|  |          | 马跃          | 2014-02-23 | MOLD NO.            |                   |
| UNIT: mm [inch]                                                                       |          |             |            | APPROVED BY:        | DATE :            |
| SCALE:1:1                                                                             | SIZE: A4 | 邱敏          | 2014-02-23 | SHEET NO.           | 1 OF 1            |