











## NOTES:

- (1) MATERIAL: STAINLESS STEEL THICKNESS=0.08MM
- (2) PRODUCT SPECIFICATIONS:
  - 2-1: CONTACT RESISTANCE: 80mΩ/MAX
  - 2-2: RATED CURRENT: 1.0A/MAX
  - 2-3: VOLTAGE RATING: 1.50V/AC/DC/MAX
  - 2-4: WELDING THRUST: ≥2.5KG
  - 2-5: DURABILITY: 1500 CYCLES
  - 2-6: OPERATING TEMPERATURE: -40°C~+85°C
- (3): FORCE: 0.50N MIN, ON CONTACT POINT
- (4): SALT SPRAY: 24 HOURS
- (5): FINISH: CONTACT AREA PLATING 3u"AU MIN, SOLDER AREA PLATING G&F MIN, 30~100u"MIN NICKEL UNDER PLATING OVER ALL.
- (6): REQUIREMENTS
  - 6-1: TERMINAL TO EAT FULL TIN, NOT PEELING, WELDING OBVIOUS COLOR AND OTHER ADVERSE
  - 6-2: ROHS, REACH, HF HALOGEN ADVERSE OF DOMESTIC AND INTERNATIONAL ENVIRONMENTAL REQUIREMENTS



RECOMMENDED PCB LAYOUT  
TOLERANCE±0.05 (焊盘推荐图)



METAL MASK T=0.10  
TOLERANCE±0.05 (钢网推荐图)



深圳市华宇创精密电子有限公司

|                                                                           |                    |                      |                                      |  |
|---------------------------------------------------------------------------|--------------------|----------------------|--------------------------------------|--|
| TOLERANCE:<br>X.X ±0.30<br>X.XX ±0.25<br>X.XXX ±0.15<br>X' ±2" X.X' ±0.5" | DRAWN BY :<br>陈一鸣  | DATE :<br>2014-02-23 | PART NAME:<br>天线弹片 L1.90*W1.00*H3.50 |  |
|                                                                           | CHECKED BY:<br>马跃  | DATE :<br>2014-02-23 | PART NO.<br>HWCW-TXT191035A          |  |
| UNIT: mm [inch]<br>SCALE:1:1 SIZE: A4                                     | APPROVED BY:<br>邱敏 | DATE :<br>2014-02-23 | DRAW NO:<br>HVC-2412191639           |  |
|                                                                           |                    |                      | SHEET NO.<br>1 OF 1                  |  |