






Pin Assignments


PIN	Name
C1	Vcc
C2	RST
C3	CLK
C4	Reserved
C5	GND
C6	Vpp
C7	I/O
C8	Reserved



NOTE:

△ Material & Finish See Table;

2. Circuit Diagram For Switch



3. Characteristic:

- 3-1. Current Rating :1A max.
- 3-2. Contact Resistance:100mOhms max
- 3-3. Insulation Resistance:100MOhms min./500VDC
- 3-4. Dielectric Withstanding Voltage:500VAC/1minute
- 3-6. Durability: 2000 Cycles
- 3-7. Operating Temperature:-25° C to+85° C

4. Please Contact PROMAX Sales Representative to Verify Product Details.

4	Shell	Stainless Steel	Nickel Under Plated Overall. g/f plated on solder tails
3	Housing	Thermoplastics	Black, UL94V-0
2	Detect	Copper Alloy	Gold Flash on Solder Tails and Contact Area; Nickel Under Plated Overall.
1	Terminal	Copper Alloy	Gold Flash on Solder Tails and Contact Area; Nickel Under Plated Overall.
Item	Part Name	Material	Description



深圳市华宇创精密电子有限公司

TOLERANCE: XX ±0.30 XXX ±0.25 XXX ±0.15 X° ±2° X.X° ±0.5°	DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: MICRO SIM 8+1P 1.24H
	CHECKED BY: 马跃	DATE : 2014-02-23	PART NO. HYCW338-SIM09-124B
UNIT: mm [inch] SCALE:1:1 SIZE: A4	APPROVED BY: 邱敏	DATE : 2014-02-23	DRAW NO: HYC-2303281506
			SHEET NO. 1 OF 1