

# 广州市东裕光电科技有限公司

# 产品规格书SPECIFICATION

客户名称 CUSTOMER	
产品名称 PRODUCTION	红外接收头
产品型号 MODEL	DYWH-IRM56384
版本号 VERSION NO	A1.0

厂址(Add): 广东省广州市番禺区石基镇海涌路 3 号 10 号厂房 2 楼

电话(Tel): 18038161512

传真(Fax): 020-39966833

网址(Net): www.tonyuled.com www.tonyuled.com





客户确认	审 核	编 制
CUSTOMER CONFIRMATION	CHECKED BY	PREPARED BY
	邓晓军	陈少龙



### **Features**

- · High protection ability against EMI.
- · Circular lens to improve the receive characteristic.
- · Line-up for various center carrier frequencies.
- · Low voltage and low power consumption.
- · High immunity against ambient light.
- · Photodiode with integrated circuit.
- TTL and CMOS compatibility.
- · Long reception distance.
- High sensitivity.
- · Pb free



TheDYWH-IRM56384 device are miniature type infrared remote control system receiver which has been developed and designed by utilizing the most updated IC technology.


The PIN diode and preamplifier are assembled on lead frame, the epoxy package is designed as an IR filter.

The demodulated output signal can directly be decoded by a microprocessor.

# **Applications**

- · Light detecting portion of remote control
- AV instruments such as Audio, TV, VCR, CD, MD, etc.
- Home appliances such as Air-conditioner, Fan, etc.
- The other equipments with wireless remote control.
- CATV set top boxes
- Multi-media Equipment

# **Application Circuit**




RC Filter should be connected closely between Vcc pin and GND pin.



## Pin Configuration

- 1. OUT
- 2. GND
- 3. V<sub>S</sub>

### **Block Diagram**







# Parts Table


# **Package Dimenstions**

(Dimensions in mm)



- ① OUTPUT
- 2 GND
- 3 Vcc





### Notes:

Tolerances unless dimensions ±0.3mm.



# Absolute Maximum Ratings (T<sub>a</sub>=25°C)

Parameter	Symbol	Rating	Unit
Supply Voltage	Vcc	6	V
Operating Temperature	Topr	-25 ~ +85	$^{\circ}\!\mathbb{C}$
Storage Temperature	Tstg	-40 ~ +85	$^{\circ}\!\mathbb{C}$
Soldering Temperature *1	Tsol	260	$^{\circ}\!\mathbb{C}$

<sup>\*1 4</sup>mm from mold body less than 10 seconds

# Electro-Optical Characteristics (Ta=25° and Vcc=3.0V)

Parameter	Symbol	MIN.	TYP.	MAX.	Unit	Condition	
Consumption Current	Icc			2	mA	No signal input	
B.P.F Center Frequency	Fo		38		KHz		
Peak Wavelength	λp		940		nm		
D i Di	$L_0$	14					
Reception Distance	$L_{45}$	6			m		
Half Angle(Horizontal)	$\Theta_h$		45		deg	At the ray axis Notes 1	
Half Angle(Vertical)	$\Theta_{\rm v}$		45		deg		
High Level Pulse Width	$T_{H}$	400		800	$\mu$ s	At the ray axis	
Low Level Pulse Width	$T_{ m L}$	400		800	$\mu$ s	Notes 2	
High Level Output Voltage	V <sub>H</sub>	2.7			V		
Low Level Output Voltage	$V_{L}$		0.2	0.5	V		

<sup>\*2.</sup> The ray receiving surface at a vertex and relation to the ray axis in the range of  $\theta=0^{\circ}$  and  $\theta=45^{\circ}$ .

<sup>\*3.</sup> A range from 30cm to the arrival distance. Average value of 50 pulses.



### **Test Method**

The specified electro-optical characteristics is satisfied under the following Conditions at the controllable distance.

- 1. Measurement place
  - A place that is nothing of extreme light reflected in the room.
- 2. External light

Project the light of ordinary white fluorescent lamps which are not high Frequency lamps and must be less then 10 Lux at the module surface. ( $Ee \le 10Lux$ )

3. Standard transmitter

A transmitter whose output is so adjusted as to **Vo=400mVp-p** and the output Wave form shown in Fig.-1.According to the measurement method shown in Fig.-2 the standard transmitter is specified. However, the infrared photodiode to be used for the transmitter should be  $\lambda p=940nm, \Delta \lambda=50nm$ . Also, photodiode is used of PD438B (Vr=5V). (Standard light / Light source temperature 2856°K).

4. Measuring system According to the measuring system shown in Fig.-3

Fig.-1 Transmitter Wave Form

D.U.T output Pulse






Fig.-2 Measuring Method

Fig.-3 Measuring System







# **Typical Performance Curves**

Fig.-4 Relative Spectral Sensitivity vs. Wavelength




Fig.-5 Relative Transmission Distance vs. Direction




Fig.-6 Output Pulse Length vs. Arrival Distance




Fig.-7 Arrival Distance vs. Supply Voltage






Fig.-8 Relative Transmission Distance

Center Carrier Frequency

100

90

90

80

60

25

30

35

40


45

50

Center Carrier Frequency (kHz)

VS.

Fig.-9 Arrival Distance vs. Ambient Temperature



# **Packing Quantity**

1500 pcs / Box

10 Boxes / Carton

# **DISCLAIMER**

- Above specification may be changed without notice. TONYU will re serve authority on material change for above specification.
- 2. When using this product, please observe the absolute maximum ratings and the instructions for use outlined in these specification sheets. TONYU assumes no responsibility for any damage resulting from use of the product which does not comply with the absolute maximum ratings and the instructions included in these specification sheets.
- 3. These specification sheets include materials protected under copyright of TONYU. Reproduction in any form is prohibited without t he specific consent of TONYU.