



REV.	ECN NO.	DESCRIPTION	DATE	DESIGN

NOTES:

- 1.BASE: LCP
- 2.PIN: Brass
- 3.Solder Tab: Brass

SPECIFICATIONS:

- 1.Spacing: 1.25
- 2.Voltage Rating: 125V AC DC
- 3.Current Rating: 1A AC,DC
- 4.Insulation Resistance: 100MΩ Min
- 5.Contact Resistance: 20mΩ Max
- 6.Withstanding voltage: 500V AC 1/Minute
- 7.Temperatuer Range: -25℃ ~+ 85℃

Part No	Pin	A	B	C
DGH-SM02B-43	2	1.25	5.75	3.75
DGH-SM03B-43	3	2.50	7.00	5.00
DGH-SM04B-43	4	3.75	8.25	6.25
DGH-SM05B-43	5	5.00	9.50	7.50
DGH-SM06B-43	6	6.25	10.75	8.75
DGH-SM07B-43	7	7.50	12.00	10.00
DGH-SM08B-43	8	8.75	13.25	11.25
DGH-SM09B-43	9	10.00	14.50	12.50
DGH-SM10B-43	10	11.25	15.75	13.75
DGH-SM11B-43	11	12.50	17.00	15.00
DGH-SM12B-43	12	13.75	18.25	16.25
DGH-SM13B-43	13	15.00	19.50	17.50
DGH-SM14B-43	14	16.25	20.75	18.75
DGH-SM15B-43	15	17.50	22.00	20.00
DGH-SM16B-43	16	18.75	23.25	21.25

TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd		
X.X ±0.30	X.* ±5°	PART NO. DGH-SMXB-43	TITLE: WAFER GH1.25 贴片带扣	
.XX ±0.20	X.X* ±3°		MANUFACTURE DWG	
.XXX ±0.10	X.XX* ±1°			
UNITS	mm	DESIGN: Ethan		
MATERILA	— — —	CHED: Olvia		
FINISH	— — —	APPD: Ava		
			SCALE N:A	SHEET 1/1

