



SUGGESTED PCB LAYOUT
(COMPONENT SIDE)

技术要求:

1. 塑件材料: PA66(UL-94V-0)
2. 接触件: 黄铜镀锡
3. 接触电阻: $\leq 10m\Omega$
4. 绝缘电阻: $>100M\Omega$
5. 额定电压: 250V AC DC
6. 额定电流: 2.0A AC DC
7. 耐压: 能承受 1000V AC/Minute
8. 工作温度: $-25^{\circ}\sim+85^{\circ}$
9. 可焊性试验: 浸锡面积 $\geq 95\%$ 温度 $235\pm 5^{\circ}$, 时间 2.5 ± 0.5 秒
10. 铅和镉等六大有害物质含量要符合环保要求。

REV.	ECN NO.	DESCRIPTION	DATE	DESIGN

Part No	Pin	A	B
APH-2A-11	2	2.00	6.00
APH-3A-11	3	4.00	8.00
APH-4A-11	4	6.00	10.00
APH-5A-11	5	8.00	12.00
APH-6A-11	6	10.00	14.00
APH-7A-11	7	12.00	16.00
APH-8A-11	8	14.00	18.00
APH-9A-11	9	16.00	20.00
APH-10A-11	10	18.00	22.00
APH-11A-11	11	20.00	24.00
APH-12A-11	12	22.00	26.00
APH-13A-11	13	24.00	28.00
APH-14A-11	14	26.00	30.00
APH-15A-11	15	28.00	32.00
APH-16A-11	16	30.00	34.00
APH-17A-11	17	32.00	36.00
APH-18A-11	18	34.00	38.00
APH-19A-11	19	36.00	40.00
APH-20A-11	20	38.00	42.00

2	端子Contact	黄铜	N*1	电镀(锡): 整个表面镀底镍 30u"MIN, 再镀锡80u"MIN
1	基座Wafer	PA66(UL94V-0)	1	白色
序号	名称	材料	数量	备注

TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd		
X.X	±0.20	X.*	±10°	PART NO.
.XX	±0.10	.X*	± 8°	APH-XA-11
.XXX	±0.05	.XX*	± 5°	TITLE: PH2.0MM 直针
UNITS	mm	DESIGN:	Ethan	MANUFACTURE DWG
MATERILA	— — —	CHED:	Olvia	
FINISH	— — —	APPD:	Ava	
				SCALE N:A
				SHEET 1/1