

TDS:EMIC

拓 電 半 導 體

自主封測 品質把控 售後保障

WEB | WWW.TDSEMIC.COM



電源管理



顯示驅動



二三極管



LDO穩壓器



觸摸芯片



MOS管



運算放大器



存儲芯片



MCU



串口通信

LM324

產品規格說明書

QUADRUPLE OPERATIONAL AMPLIFIERS


DESCRIPTION

The LM324 consists of four independent, high gain, internally frequency compensated operational amplifiers which were designed specifically to operate from a single power supply over a wide range of voltages. Operation from split power supplies is also possible and the low power supply current drain is independent of the magnitude of the power supply voltage.

Application areas include transducer amplifiers, DC gain blocks and all the conventional op amp circuits.

FEATURES


- Wide range of supply voltages
- Low supply current drain independent of supply voltage
- Low input biasing current
- Low input offset voltage and offset current
- Input common-mode voltage range includes ground
- Differential input voltage range equal to the power supply voltage
- DC voltage gain 100 V/ mV Typ
- Internally frequency compensation



ORDERING INFORMATION

DEVICE	Package Type	MARKING	Packing	Packing Qty
LM324N	DIP-14	LM324	TUBE	1000pcs/Box
LM324M/TR	SOP-14	LM324	REEL	2500pcs/Reel
LM324MT/TR	TSSOP-14	LM324	REEL	2500pcs/Reel

PACKAGE INFORMATION



DIP-14/SOP-14/TSSOP-14

ELECTRICAL CHARACTERISTICS

at specified free-air temperature, VCC = 5V (unless otherwise noted)

PARAMETER	TEST CONDITIONS*		LM324			UNIT
			MIN	TYP	MAX	
VIO Input offset voltage	Vcc = 5V to MAX, VIC = VICRmin, VO = 1.4V	25°C		3	7	mV
		Full temperature range			9	
α VIO Average temperature coefficient of input offset voltage		Full temperature range		7		$\mu\text{V}/^\circ\text{C}$
IIO Input offset current	Vo = 1.4V	25°C		2	50	nA
		Full temperature range			150	
α IIO Average temperature coefficient of input offset current		Full temperature range		10		$\text{pA}/^\circ\text{C}$
IIB Input bias current	Vo = 1.4V	25°C		-20	-250	nA
		Full temperature range			-500	
VICR Common-mode input voltage range	Vcc = 5V to MAX	25°C	0 to Vcc-1.5			V
		Full temperature range	0 to Vcc - 2			
VOH High-level output voltage	RL = 2 k Ω	25°C	Vcc-1.5			V
	Vcc = MAX, RL = 2k Ω	Full temperature range	26			
	Vcc = MAX, RL = 10 k Ω	Full temperature range	27	28		
VOL Low-level output voltage	RL = 10 k Ω	Full temperature range		5	20	mV
AVD	Vcc = 15 V,	25°C	25	100		V/mV


Large-signal differential voltage amplification	$V_o=1V$ to 11 V, $R_L \geq 2\text{ k}\Omega$	Full temperature range	15			
CMRR Common-mode rejection ratio	$V_{CC} = 5V$ to MAX, $V_{IC} = V_{ICR\text{ min}}$	25°C	65	80		dB
kSVR Supply voltage rejection ratio ($\Delta V_{CC}/\Delta V_{IO}$)	$V_{CC} = 5V$ to MAX	25°C	65	100		dB
V_{o1}/V_{o2} Crosstalk attenuation	$f=1\text{kHz}$ to 20 kHz	25°C		120		dB
IO Output current	$V_{CC} = 15\text{ V}$, $V_{ID}=1V, V_o=0$	25°C	-20	-30		mA
		Full temperature range	-10			
	$V_{CC} = 15\text{ V}$, $V_{ID}= -1V, V_o=15V$	25°C	10	20		
		Full temperature range	5			
	$V_{ID}= -1V$, $V_o = 200\text{ mV}$	25°C	12	30		μA
I_{OS} Short-circuit output current	V_{CC} at 5 V, GND at -5V, $V_o=0$	25°C		± 40	± 60	mA
I_{CC}	$V_o = 2.5\text{ V}$, No load	Full temperature range		1.5	2.4	mA
Supply current (four amplifiers)	$V_{CC} = \text{MAX}$, $V_o = 0.5V_{CC}$, No load	Full temperature range		1.1	3	

* All characteristics are measured under open loop conditions with zero common-mode input voltage unless otherwise specified.

"MAX" V_{CC} for testing purposes is 30 V. Operating temperature -40~ 85° C, MAX Junction temperature + 125°C.


PHYSICAL DIMENSIONS

DIP-14




Dimensions In Millimeters(DIP-14)										
Symbol:	A	B	D	D1	E	L	L1	a	c	d
Min:	6.10	18.94	8.10	7.42	3.10	0.50	3.00	1.50	0.40	2.54 BSC
Max:	6.68	19.56	10.9	7.82	3.55	0.70	3.60	1.55	0.50	

SOP-14



Dimensions In Millimeters(SOP-14)									
Symbol:	A	A1	B	C	C1	D	Q	a	b
Min:	1.35	0.05	8.55	5.80	3.80	0.40	0°	0.35	1.27 BSC
Max:	1.55	0.20	8.75	6.20	4.00	0.80	8°	0.45	

TSSOP-14



Dimensions In Millimeters(TSSOP-14)									
Symbol:	A	A1	B	C	C1	D	Q	a	b
Min:	0.85	0.05	4.90	6.20	4.30	0.40	0°	0.20	0.65 BSC
Max:	0.95	0.20	5.10	6.60	4.50	0.80	8°	0.25	