


◆Scope

This specification applies to the SLO160808T Series of SMD power inductors.


◆Lead Free PartNumbering

CMLO	160808	T	1R0	M	T	T
(1)	(2)	(3)	(4)	(5)	(6)	(7)

- (1) Series Type
- (2) Dimension: LxWxH
- (3) Material Code
- (4) Inductance: R68=0.68uH; 1R0=1.0uH
- (5) Inductance Tolerance: M=±20%, N=±30%
- (6) Company Code
- (7) Packaging: packed in embossed carrier tape




◆Dimensions



Series	L(mm)	W(mm)	H(mm)	F(mm)	Recommended Land Patterns		
					A(mm)	B(mm)	E(mm)
SLO160808T	1.6±0.2	0.8±0.2	0.8Max.	0.5±0.2	0.5Typ.	1.7Typ.	0.9Typ.

◆Structural drawing



No.	Component	Material
①	Body	Alloy material
②	Winding	Enamelled Wire
③	Shield	Epoxy
④	Electric	Base plating-Cu Base plating-Ni Base plating-Sn

◆ Specification

Part No.	Inductance Ls(uH)	Direct Current Resistance DCR(mΩ)		Temperature Rise Current Irms(A)		Saturation Current Isat(A)	
		Typ	Max.	Typ	Max.	Typ	Max.
SLO160808TR22MTT	0.22±20%	33	40	3.4	3.0	5.5	5.0
SLO160808TR24MTT	0.24±20%	34	41	3.3	2.9	5.3	4.8
SLO160808TR33MTT	0.33±20%	30	35	4.7	4.3	4.7	4.4
SLO160808TR47MTT	0.47±20%	80	100	2.6	2.3	4.1	3.7
SLO160808TR56MTT	0.56±20%	85	110	2.2	1.9	4.0	3.5
SLO160808TR68MTT	0.68±20%	110	130	2.1	1.9	3.3	3.0
SLO160808T1R0MTT	1.00±20%	180	200	2.1	1.8	3.0	2.6
SLO160808T1R5MTT	1.50±20%	240	285	1.7	1.4	2.4	2.0
SLO160808T2R2MTT	2.20±20%	220	260	1.4	1.2	1.5	1.3
SLO160808T3R3MTT	3.30±20%	500	600	1.0	0.9	1.4	1.2
SLO160808T4R7MTT	4.70±20%	585	700	1.0	0.8	1.2	1.0
SLO160808T100MTT	10.0±20%	1450	1600	0.5	0.45	0.8	0.7

Test condition & equipment :

Item	Test condition	Test equipment
Ls	1MHz/1V	HP4263BIM3532-50 or equivalent
DCR	direct-current	HP4263BRM3545 or equivalent
Isat	1MH/1V	Microtest 6379 &6220 or equivalent
Irms	ambient temperature 20°C	Microtest 6379 &6220 or equivalent

Isat: The DC current at which the inductance drops approximate 30% from its value without current, Load current time within Ls.

Irms: The DC current is inductor surface temperature to rise by 40°C.

◆ Operating Temperature Range

-40°C~+125°C, Including self-heating


◆ Storage Conditions

Store products in a warehouse in compliance with the following condition:

Temperature: Inductors (product with taping) -10 to +40°C;

Inductors body -40 to +85°C.

Humidity: 30~70%RH

◆ RECOMMENDED REFLOW PROFILE


Preheating			Soldering		Peak	
Temp.		Time	Temp.	Time	Temp.	Time
T1	T2	t1	T3	t2	T4	t3
150°C	180°C	60 to 120s	230°C	30 to 50s	250 to 260°C	10s max

◆ Reliability Mechanical

序号 No.	项目 Items	要求 Requirements	试验方法及备注 Test Methods and Remarks
1	绝缘电阻 Insulation Resistance	$\geq 100\text{M}\Omega$	在电感器线圈和本体顶面中间施加 100 V 直流电压保持60 s。 100 V DC between inductor coil and The middle of the top surface of the body for 60 seconds.
2	可焊性 Solderability	电极面90%以上覆盖新的焊料。 90% or more of electrode area shall be coated by new solder.	在 $(245\pm 5)^{\circ}\text{C}$ 熔融的焊锡 (96.5Sn/3.0Ag/0.5Cu) 中浸 (5 ± 1) s。 Dip pads in flux and dip in solder pot (96.5Sn/3.0Ag/0.5Cu) at $(245\pm 5)^{\circ}\text{C}$ for (5 ± 1) seconds.
3	耐焊接热 Resistance to Soldering Heat	外观无可见机械损伤; 电感量变化率: $\pm 10\%$ 以内。 No visible mechanical damage. Inductance change: Within $\pm 10\%$	在 $(260\pm 5)^{\circ}\text{C}$ 熔融的焊锡 (96.5Sn/3.0Ag/0.5Cu) 中浸 (10 ± 1) s。 Dip pads in flux and dip in solder pot (96.5Sn/3.0Ag/0.5Cu) at $(260\pm 5)^{\circ}\text{C}$ for (10 ± 1) seconds.
4	端子强度 Adhesion of terminal electrode	元件的端子与本体结合无松动、无脱落。 Strong bond between the pad and the core, without come off PC board.	将电感器用 $(260\pm 5)^{\circ}\text{C}$, (20 ± 5) s 焊在带有 0.3 mm 厚锡膏的基板上, 然后用治具垂直电极面方向加压 10 N, (10 ± 1) s。 Inductors shall be subjected to $(260\pm 5)^{\circ}\text{C}$ for (20 ± 5) s Soldering in the base whit 0.3mm solder. And then aplomb electrode way plus tax 10 N for (10 ± 1) seconds.
5	耐高温 High temperature	外观无可见机械损伤; 电感量变化率: $\pm 10\%$ 以内。 No visible mechanical damage. Inductance change: Within $\pm 10\%$	温度 $(+85\pm 2)^{\circ}\text{C}$, 时间 (96 ± 2) h; Temperature is $(+85\pm 2)^{\circ}\text{C}$ and keep (96 ± 2) hours.
6	耐低温 Low temperature	外观无可见机械损伤; 电感量变化率: $\pm 10\%$ 以内。 No visible mechanical damage. Inductance change: Within $\pm 10\%$	温度 $(-40^{\circ}\text{C} \pm 2)^{\circ}\text{C}$, 时间 (96 ± 2) h; Temperature is $(-40\pm 2)^{\circ}\text{C}$ and keep (96 ± 2) hours.

序号 No.	项目 Items	要求 Requirements	试验方法及备注 Test Methods and Remarks
7	温度变化 Thermal shock	外观无可见机械损伤；电感量变化率：±10%以内。 No visible mechanical damage. Inductance change: Within ±10%	(-40±3) °C, 时间(30±3) min ↔ (125°C±2) °C/(30±3) min, 转换时间(2~3) min, 循环32次；在室温下放置 2 小时后、48 小时内测试。 The test sample shall be placed at (-40±3)°C and (125±2)°C for (30±3) min, different temperature conversion time is 2~3 minutes. The temperature cycle shall be repeated 32 cycles. Placed at room temperature for 2 hours, within 48 hours of testing.
8	温度特性 Temperature characteristic	电感量变化率 P_{c-b}, P_{c-d} 不超过 ±20%。 Inductance change P_{c-b}, P_{c-d} : Within ±20%	a: +20 °C (30~45) min → b: -40 °C (30~45) min → c: +20 °C (30~45) min → d: +125 °C (30~45) min → e: +20 °C (30~45) min $P_{c-b} = \frac{L_b - L_c}{L_c} \times 100\% ; \quad P_{c-d} = \frac{L_d - L_c}{L_c} \times 100\%$
9	恒定湿热 Static Humidity	外观无可见机械损伤； 电感量变化率：±10%以内。 No visible mechanical damage. Inductance change: Within ±10%	将电感器放置在于湿度(93±3)%RH, 温度(40±2) °C 的环境中存放(1000±2) h, 在室温下放置2 小时后、48 小时内测试。 Inductors shall be subjected to (93±3)%RH . at (60±2)°C for (96±2) h . Placed at room temperature for 2 hours, within 48 hours of testing.
10	耐久性 (寿命) Life	外观无可见机械损伤； 电感量变化率：±10%以内。 No visible mechanical damage. Inductance change: Within ±10%	温度(85±2)°C, 时间(1000±24) h, 施加 Irms, 在室温下放置2 小时后、48 小时内测试。 Inductors shall be store at (85±2)°C for (1000±24) hours with Irms applied. Placed at room temperature for 2 hours, within 48 hours of testing.

Technical drawing of a circular mechanical part, showing front and side views with dimensions in mm.

Front View Dimensions:

- Overall Diameter: $\varnothing 180 \pm 2.0$
- Central Hole Diameter: $\varnothing 13 \pm 0.2$
- Flange Thickness: 10
- Spoke Width: 2.0 ± 0.5
- Inner Hub Diameter: $\varnothing 21 \pm 0.8$

Side View Dimensions:

- Overall Height: 14.4 max
- Central Hole Diameter: $\varnothing 60$ min
- Flange Thickness: $8.4^{+2}_{-0.0}$

Dimensions in mm

Technical drawing of a sprocket part showing dimensions in mm. The drawing includes a side view on the left and a top view on the right. The side view shows a U-shaped profile with dimensions K (total height) and B (height of the lower flange). The top view shows a rectangular plate with a wavy left edge, five circular sprocket holes, and four rectangular cavities. Dimensions include: sprocket hole diameter $1.5^{+0.1}_{-0.1}$, hole-to-hole pitch 2.0 ± 0.05 , distance from center to edge 4.0 ± 0.1 , hole-to-cavity distance 4.0 ± 0.1 , cavity width 1.75 ± 0.1 , cavity-to-edge distance 3.5 ± 0.05 , and total width 8.0 ± 0.3 . Labels include 'Sprocket hole' and 'Cavity'.

Dimensions in mm

160min. Taping 200min.

Drawing direction

300min.

Dimensions in mm

3000 pcs/reel