




All PCB Power Relay: 30 Amp, Monostable DC (57)

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts

TE Part # 63435-1
250 FASTON REC 14-10 AWG SPBR

TE Part # 63306-2
250 FASTON REC 18-14 AWG TPBR

TE Part # 2238209-3
250 FASTON,FLAG,REC.,22-12 AWG, PTBR

Also in the Series | **Potter & Brumfield T9A**

DC Relays(56)

Electromechanical Relays(57)

Customers Also Bought

TE Part #1-282858-2
12P. TERMI-BLOK PCB MOUNT 90

TE Part #2842104-8
8P,2MM,BRK HDR,SRVT,SMD,0.76AU, TR W/CAP

TE Part #9-2176407-0
3560 39R 5%

TE Part #2316542-9
AV19 SPL 3A SPOT LOGO R&B 12V

TE Part #2-2364686-4
AVH22 FLT SS LK RNG R&G 24V16A

TE Part #1-2329360-9
PB OFF/ON RC GRE M4 TERM. IP68

TE Part #T1349160120-000
H16A-TGH-M20

TE Part #2273120-3
M12 angled plug to M12 strgt socket AA



Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_7-1423091-0_K.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_7-1423091-0_K.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_7-1423091-0_K.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

T9A Relay Datasheet

English

Product Specifications

Definitions General Purpose Relays

English

Agency Approvals

Agency Approval Document

English