


# UPCV3K-F - Flange

1881202

<https://www.phoenixcontact.com/us/products/1881202>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



**Flange**, fitted on the left and right of UPCV3K 4-G-7,62, for a reliable screw connection with plugs with a screw flange

## Your advantages

- Can be plugged into PC 4 and PC 5 plugs
- Vibration-resistant connection with flange terminal blocks that can be aligned (-F)
- UPCV3K provides three plug outlets per terminal point
- For mounting on NS 35/... and NS 15... DIN rails in accordance with EN 60715 - or in the case of the UPCV3K 4-G-7,62 - for mounting on NS 35/... and NS 32 DIN rails

## Commercial data

Item number	1881202
Packing unit	50 pc
Minimum order quantity	50 pc
Sales key	BE12
Product key	BE1241
Catalog page	Page 441 (C-3-2013)
GTIN	4017918340797
Weight per piece (including packing)	13.25 g
Weight per piece (excluding packing)	12.256 g
Customs tariff number	39269097
Country of origin	PL

# UPCV3K-F - Flange

1881202

<https://www.phoenixcontact.com/us/products/1881202>



## Technical data

### Product properties

Product type	Flange
Product family	PCVK 4
Number of positions	1
Pitch	7.62 mm

### Dimensions

Width	7.62 mm
Height	74.5 mm
Depth on NS 35/7,5	41 mm
Pitch	7.62 mm

### Material specifications

Color	gray (RAL 7042)
Flammability rating according to UL 94	V0
Insulating material	PA
Contact surface	Tin Sn

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-60 °C (max. operating temperature see derating curve)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (storage/transport)	30 % ... 70 %

### Mounting

Mounting type	NS 35/7,5
	NS 35/15
	NS 32

# UPCV3K-F - Flange

1881202

<https://www.phoenixcontact.com/us/products/1881202>



## Classifications

### ECLASS

ECLASS-11.0	27141190
ECLASS-12.0	27141190
ECLASS-13.0	27250302

### ETIM

ETIM 9.0	EC001041
----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# UPCV3K-F - Flange

1881202

<https://www.phoenixcontact.com/us/products/1881202>



## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	c714f1cd-8987-40a5-b662-3e97239c3f75

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)