



RECOMMEND P.C.B LAYOUT
PCB TOLERANCE:±0.05 (TOP VIEW)

SPECIFICATIONS

Current Rating: 3Amps
Insulation Resistance: 1000MΩ Min
Contact Resistance: 20mΩ Max
Withstanding Voltage: AC 1000V
Operation Temperature: -40° to +105°
Contact Material: Brass
Standard: PA6T
Insulator Material: Polyester(UL 94V-0)
Contact Plating: Gold Flash
Max.Processing Temp:240°C for30-60seconds
(260°C for5seconds)

REV.	ECN NO.	DESCRIPTION	DATE	DESIGN

P/N	PIN	DIM.A	DIM.B
PZ2.54V-1101P-H25	1	0.00	2.54
PZ2.54V-1102P-H25	2	2.54	5.08
PZ2.54V-1103P-H25	3	5.08	7.62
PZ2.54V-1104P-H25	4	7.62	10.16
PZ2.54V-1105P-H25	5	10.16	12.70
PZ2.54V-1106P-H25	6	12.70	15.24
PZ2.54V-1107P-H25	7	15.24	17.78
PZ2.54V-1108P-H25	8	17.78	20.32
PZ2.54V-1109P-H25	9	20.32	22.86
.....			
PZ2.54V-1140P-H25	40	(40-1)X2.54	(40)X2.54

TOLERANCE		 深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
X.X ±0.30	X.* ±5°	PART NO. PZ2.54V-11NP-H25	TITLE: 2.54PH H2.5 1xPin 180° PC3.0 PA6.0 PB2.5 L11.5 6T		
.XX ±0.20	X.* ±1°				
.XXX ±0.10	X.XX ±0.5°				
UNITS	mm	DESIGN: Ethan	MANUFACTURE DWG		
MATERILA	— — —	CHED: Olvia			
FINISH	— — —	APPD: Ava		SCALE N:A	SHEET 1/1