



Connectors > Terminal Blocks & Strips > Terminal Block & Strip Accessories > Terminal Block & Strip Mounting & Retention Accessories



Mounting & Retention Accessory Type: **Cable Clamp**

Product Length: **50.5 mm [1.988 in]**

Operating Temperature Range: **-55 – 110 °C [-67 – 230 °F]**

EU RoHS Compliance: **Compliant**

EU ELV Compliance: **Compliant**

Features

Industry Standards

IP Rating	IP20
UL Flammability Rating	UL 94HB

Usage Conditions

Installation Temperature Range	-5 – 40 °C[23 – 104 °F]
Operating Temperature Range	-55 – 110 °C[-67 – 230 °F]

Dimensions

Product Width	9.4 mm[.37 in]
Product Depth	50.5 mm[1.988 in]
Product Height	2.4 mm[.094 in]
Product Spacing	9.4 mm[.37 in]
Product Length	50.5 mm[1.988 in]

Body Features

Product Weight	2.02 g[.071 oz]
Primary Product Color	Dark Gray



Mounting & Retention Accessory Type	Cable Clamp
-------------------------------------	-------------

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1SNK805718R0000
CDK2.5-4



TE Part # 1SNK805723R0000
CDK2.5-9











TE Part # 1SNK805743R0000
CDK2.5-BL-E



TE Part # 1SNK805744R0000
CDK2.5-J-BL



 TE Part # 1SNK805750R0000 CDK2.5-PE	 TE Part # 1SNK805713R0000 CDK2.5-E	 TE Part # 1SNK805753R0000 CDK2.5-PE-E	 TE Part # 1SNK805740R0000 CDK2.5-2P-J
 TE Part # 1SNK805720R0000 CDK2.5-6	 TE Part # 1SNK805722R0000 CDK2.5-8	 TE Part # 1SNK805717R0000 CDK2.5-3	 TE Part # 1SNK805738R0000 CDK2.5-J
 TE Part # 1SNK805752R0000 CDK2.5-2P-J-PE-E	 TE Part # 1SNK805724R0000 CDK2.5-10	 TE Part # 1SNK805748R0000 CDK2.5-J-PE	 TE Part # 1SNK805745R0000 CDK2.5-J-BL-E
 TE Part # 1SNK805721R0000 CDK2.5-7	 TE Part # 1SNK805719R0000 CDK2.5-5	 TE Part # 1SNK805746R0000 CDK2.5-2P-J-BL	 TE Part # 1SNK805742R0000 CDK2.5-BL

Customers Also Bought

 TE Part #M902-2163 BKSHL, 6SZ, CBL SZ .430-.570, HD10	 TE Part #DT04-4P REC, 4P, GRY, N	 TE Part #1SNK805738R0000 CDK2.5-J	 TE Part #1SNK805739R0000 CDK2.5-J-E
---	--	---	---



Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1SNK900660R0000_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1SNK900660R0000_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1SNK900660R0000_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

PT-ZD

English

SNK SERIES TERMINAL BLOCKS

English

ENTRELEC Terminal Block - Master Catalog

ENTRELEC Terminal Block - Master Catalog

English