HF115F-A

MINIATURE HIGH POWER RELAY

5kV dielectric strength (between coil and contacts)

Meeting VDE 0700, 0631 reinforce insulation

Plastic sealed and flux proofed types available

Product in accordance to IEC 60335-1 available

RoHS compliant

Features

• AC voltage coil type 16A switching capability 1 & 2 pole configurations

Low height: 15.7 mm Creepage distance: 10mm

Sockets available

UL insulation system: Class F





(CQC)



File No.:CQC1702176311

CONTACT DATA

Contact arrangement	1A, 1B, 1C	2A, 2B, 2C			
Contact resistance 1)	100mΩ max.(at 1A 6VDC)				
Contact material	See"ORDERING INFORMATION"				
Contact rating (Res. load)	12A/16A 250VAC	8A 250VAC			
Max. switching voltage	440VAC / 300VDC				
Max. switching current	12A / 16A	8A			
Max. switching power	3000VA / 4000VA	2000VA			
Mechanical endurance		1 x 10 ⁶ 0PS			
Electrical endurance	H3B type: 5 x 10 ⁴ oPs (16A 250 Resistive load, Room temp., 1s on 9 2H4B type: 5 x 10 ⁴ oPs (8A 250 Resistive load, Room temp., 1s on 9				

COIL	
Coil power	Approx. 0.75VA

COIL	DATA (at		at 23°C			
Nominal Voltage VAC	Pick-up Voltage VAC max. ¹⁾	Drop-out Voltage VAC min. ¹⁾	Coil Current mA	Coil DC Resistance Ω		
24	18.00	3.60	31.6	350 x (1±10%)		
115	86.30	17.30	6.6	8100 x (1±15%)		
230	172.50	34.50	3.2	32500 x (1±15%)		
Notes: 1) The data shown above are initial values.						

Notes: 1) The data shown above are initial values.

CHARACTERISTICS

Insulation resistance			1000MΩ (at 500VDC)
Dielectric	Between coil & contacts		5000VAC 1min
2.0.000.00	Between	open contacts	1000VAC 1min
strength	Between contact sets		2500VAC 1min
Temperatu	ure rise (at	nomi. volt.)	85K max.
Shock resistance *		Functional	98m/s ²
		Destructive	980m/s²
Vibration r	esistance	10Hz to150Hz 10g/5g	
Humidity			5% to 85% RH
Ambient te	emperature	-40°C to 70°C	
Terminatio	n	PCB	
Unit weight			Approx. 13.5g
Construction			Plastic sealed, Flux proofed
-			

Notes: 1) The data shown above are initial values. 2) * Index is not that of relay length direction. SAFETY APPROVAL RATINGS

	12A 250VAC
UL/CUL	16A 250VAC
	8A 250VAC
VDE	12A 250VAC at 70°C
(AqNi, AqNi+Au)	16A 250VAC at 70°C
	8A 250VAC at 70°C
VDE	12A 250VAC at 70°C
(AgSnO ₂ , AgSnO ₂ +Au)	8A 250VAC at 70°C

Notes: 1) All values unspecified are at room temperature. 2) Only typical loads are listed above. Other load specifications can be available upon request.



HONGFA RELAY ISO9001, IATF16949 , ISO14001, ISO45001, IECQ QC 080000, ISO/IEC 27001 CERTIFIED 2023 Rev. 2.01

ORDERING INFORMATION								
HF	024	-1H	S	1	Α	F	(XXX)	
Туре								
Coil voltage	24, 115, 230VAC	-						
Contact arrangement	1H: 1 Form A 1D: 1 Form B 1Z 2H: 2 Form A 2D: 2 Form B 2Z							
Construction ^{1) 2)}	S: Plastic sealed Nil: Flux p							
Version 1: 3.5mm 1 pole 12A 3: 5.0mm 1 pole 16A 2: 5. 4: 5.			m 1 pole m 2 pole		-			
Contact material ³⁾	erial ³⁾ A: AgSnO2 B: AgNi Nil: AgCdO G: AgCdO+Au plated AG: AgSnO2+Au plated BG: AgNi+Au plated							
Insulation standard	F: Class F							
Special code ⁴⁾	XXX: Customer speci	al requireme	ent N	Nil: Sta	ndard			_

Notes: 1) We recommend flux proofed types for a clean environment (free from contaminations like H₂S, SO₂, NO₂, dust, etc.). We suggest to choose plastic sealed types and validate it in real application for an unclean environment (with contaminations

2) Contact is recommended for suitable condition and specifications if water cleaning or surface process is involved in assembling relays

a) Contact is recommended for suitable condition and specifications if water cleaning of surface process is involved in assembling real on PCB.
b) For gold plated type, the min. switching current and min. switching voltage is 10mA 5VDC.
c) The customer special requirement express as special code after evaluating by Hongfa. e.g.(335) stands for product in accordance to IEC 60335-1 (GWT).

OUTLINE DIMENSIONS, WIRING DIAGRAM AND PC BOARD LAYOUT

Unit: mm

3.5

20.16

Outline Dimensions

3.5mm Pinning (HF115F-A/

5mm Pinning (HF115F-A/





PCB Layout (Bottom view)

3.5mm,1 Pole,12A,HF115F-A/







OUTLINE DIMENSIONS, WIRING DIAGRAM AND PC BOARD LAYOUT

Unit: mm



PCB Layout (Bottom view)





Remark: 1) In case of no tolerance shown in outline dimension: outline dimension \leq 1mm, tolerance should be ±0.2mm; outline dimension >1mm and \leq 5mm, tolerance should be ±0.3mm; outline dimension >5mm, tolerance should be ±0.4mm.

2) The tolerance without indicating for PCB layout is always ±0.1mm.

3) The width of the gridding is 2.52mm.

Wiring Diagram (Bottom view)

HF115F-A/



CHARACTERISTIC CURVES

MAXIMUM SWITCHING POWER

(V) transformation of the second seco



ENDURANCE CURVE

Breaking Capacity(kVA)

Notes:

1) Curve A: 2H4B type Curve B: 1H1B(or 1H2B) type Curve C: 1H3B type

2) Test conditions:

NO, Resistive load, 250VAC

Flux proofed, Room temp., 1s on 9s off.

COIL OPERATING RANGE (AC) *



Ambient temperature (°C)

Notes: * The use of a relay with an energising voltage other than the rated coil voltage may lead to reduced electrical life.

An energising voltage over the abver range may damage the insulation of relay coil.

Relay Sockets



Features

- The insulation resistance is $1000M\Omega$
- Three mounting types are available: PCB, screw mounting and DIN rail mounting
- With finger protection device
- Many kinds of plug-in modules are available with the function of energizing indication and wiring protection
- Environmental friendly product (RoHS compliant)

CHARACTERISTICS

type	Nominal Voltage	Nominal Current	Ambient Temperature	Dielectric Strength min.	Screw Torque	Wire Strip Length	Unit weight
14FF-2Z-A1	250VAC	10A	-40°C ~ 70°C	5000VAC	_	*	Approx.3g
14FF-2Z-C2	250VAC	10A	-40°C ~ 70°C	5000VAC	0.6N·m	7mm	Approx.39g
14FF-2Z-C3	250VAC	10A	-40°C ~ 70°C	5000VAC	0.6N∙m	7mm	Approx.45g
14FF-2Z-C4	250VAC	10A	-40°C ~ 70°C	5000VAC	_	9mm	Approx.42g
14FF-2Z-C10	300VAC/DC	10A	-40°C ~ 70°C	5000VAC	_	10mm	Approx.36g
14FF-2Z-C10/P	300VAC/DC	10A	-40°C ~ 70°C	5000VAC	—	10mm	Approx.37g

OUTLINE DIMENSIONS, WIRING DIAGRAM AND PC BOARD LAYOUT

Unit: mm



OUTLINE DIMENSIONS, WIRING DIAGRAM AND PC BOARD LAYOUT

Unit: mm



Notes: If need accesscry, please order with type.

Unit: mm

Retainer

14FF-H1(Metallic retainer)

14FF-H4 (Plastic retainer)





Ø0.7

14FF-H7 (Metallic retainer)

Marker

14FF-M1



Precautions For Use

For your personal safety and the normal operation of the equipment, as well as to prevent fire, please note the following issues: 1. The rated current of the socket should be no less than the rated current of the relay.

- 2.Sockets are required to be firmly fixed to prevent the wiring from loosening and affecting the quality of wiring.
- 3.Be sure to disconnect power to the outlet before installation, disassembly, wiring, maintenance and inspection.
- 4. Prevent foreign objects such as wire shavings from falling inside this product when wiring.

5.Be sure to install the relay in place, and use accessories such as retainer if necessary to improve contact reliability. Do not use with incomplete connections.

6.Be sure to observe the relay ratings and do not overload the relay.

Applicable conductor cross section

7.Before selecting a relay, make sure that the drive voltage matches the relay excitation voltage.

	solid wire	1×0.5/0.75/1.0/1.5/2.5 mm ²			
		2×0.5/0.75/1.0/1.5 mm ²			
	Multi-stranded wire	Multi-stranded wire without	1×0.5/0.75/1.0/1.5/2.5 mm ²		
		standard sleeve	2×0.5/0.75/1.0/1.5 mm ²		
		Multi-stranded wire	1×0.5/0.75/1.0/1.5 mm ²		
		with standard sleeve	2×0.5/0.75/1.0 mm ²		



Precautions For Use

Regarding push in socket

- The screwdriver insertion hole must not be wired.
- When inserting the screwdriver into the hole, please insert it at an angle.
- Do not twist or wiggle the screwdriver when it is in the hole, as this may cause damage the socket.
- Do not forcibly bend or pull on the wire. Otherwise it may result broken wire.
- Do not insert more than one wires into one wiring hole.
- To prevent smoke and fire from the wiring material, check the power supply rating and that the wire sleeves used are in accordance with DIN 46228-4.

```
The conductors used comply with GB/T 5023.3-2008 (IEC 60227-3) standard.
```

Recommended Wires	Film peel (when bar terminals are not used)
0.5~2.5mm2/AWG20~14	≥10mm



Things to be noticed when selecting sockets:

- 1. Please choose suitable relay socket according to the actual mounting environment, relay contact poles and terminal layout. If there is any query on selection, please contact Hongfa for the technical service;
- 2. Socket which can be mounted with markers is furnished with a marker; as for other related components, they should be selected separately.
- Please do give clear indication of the types of relay sockets and related components you choose while placing order. 3. The above is only an example of typical socket and related component type which is suitable to HF115FP relay. If you have any special requirements,
- please contact us.
- 4. Main outline dimension, outline dimension >50mm, olerance should be ±11mm;20mm <outline dimension ≤50mm,tolerance should be ±0.5mm;5mm <outline dimension≤20mm, tolerance should be ±0.4mm,outline dimension≤5mm,tolerance should be ±0.3mm;
- 5. DIN rail mounting: recommend to use standard rail 35×7.5×1mm, 35×15×1mm. When installed vertically, the coil terminal at the bottom please.

Disclaimer

The specification is for reference only. See to "Terminology and Guidelines" for more information. Specifications subject to change without notice. We could not evaluate all the performance and all the parameters for every possible application. Thus the user should be in a right position to choose the suitable product for their own application. If there is any query, please contact Hongfa for the technical service. However, it is the user's responsibility to determine which product should be used only.

© Xiamen Hongfa Electroacoustic Co., Ltd.All rights of Hongfa are reserved.