

106138-2

✓ ACTIVE


Z-PACK | Z-PACK 2mm HM

TE Internal #: 106138-2

PCB Mount Shroud, Gray, Glass Filled Polyester, 125 Position, Z-PACK 2mm HM

[View on TE.com >](#)

Connectors > Connector Accessories > Connector Caps & Covers

Connector Cover Type: **PCB Mount Shroud**Primary Product Color: **Gray**Primary Product Material: **Glass Filled Polyester**Number of Positions: **125**Operating Temperature (Max): **125 °C [257 °F]**

Features

Industry Standards

UL Flammability Rating

UL 94V-0

Housing Features

Centerline (Pitch)

2 mm[.079 in]

Dimensions

Row-to-Row Spacing

2 mm[.079 in]

Product Width

15.4 mm[.606 in]

Product Length

49.9 mm[1.965 in]

Product Height

13.46 mm[.53 in]

Mechanical Attachment

Mating Alignment Type

Multi-Purpose Center

Mating Alignment

With

Configuration Features

Number of Rows

5

Number of Positions

125

Product Type Features

Connector Cover Type

PCB Mount Shroud

Body Features

Primary Product Color

Gray

Primary Product Material

Glass Filled Polyester

Usage Conditions

Operating Temperature (Max)

125 °C[257 °F]

Operating Temperature Range

-55 – 125 °C[-67 – 257 °F]

Other

EU RoHS Compliance

Compliant

EU ELV Compliance

Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU

Compliant

EU ELV Directive 2000/53/EC

Compliant

China RoHS 2 Directive MIIT Order No 32, 2016

No Restricted Materials Above Threshold

EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JUNE 2024 (241)
 Candidate List Declared Against: JUNE 2024 (241)
 Does not contain REACH SVHC

Halogen Content

Not Low Halogen - contains Br or Cl > 900 ppm.

Solder Process Capability

Not applicable for solder process capability







Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Also in the Series | Z-PACK 2mm HM



Customers Also Bought





Documents

Product Drawings

Z-PACK/B SHRD.125P.

English

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_106138-2_A.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_106138-2_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_106138-2_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English