





| 标记 MARK | ECN编号/变更内容 ECN NO/DEFINITION | 修改 REVISE | 日期 DATE | 核准 APPROVE |
|------------|---------------------------------|--------------|------------|---------------|
| | | | | |
| | | | | |

| Pin | DIM A | DIM B |
|-----|-------|-------|
| 2 | 3.96 | 7.92 |
| 3 | 7.92 | 11.88 |
| 4 | 11.88 | 15.84 |
| 5 | 15.84 | 19.80 |
| 6 | 19.80 | 23.76 |
| 7 | 23.76 | 27.72 |
| 8 | 27.72 | 31.68 |
| 9 | 31.68 | 35.64 |
| 10 | 35.64 | 39.60 |
| 11 | 39.60 | 43.56 |
| 12 | 43.56 | 47.52 |



技术要求:

适应基板厚度: 1.2mm~1.6mm
温度范围: -25°C~85°C
额定电压: 250V AC/DC
额定电流: 7A
接触电阻: ≤0.01Ω
绝缘电阻: ≥1000MΩ
耐压: 1500V AC/minute

| | | | | |
|----|----|------|-------|----|
| 2 | 插针 | 铜 | 镀锡 | |
| 1 | 基座 | PA66 | 白色 | |
| 序号 | 品名 | 材质 | 电镀/颜色 | 备注 |

| | | | |
|--|-------------|---------------|--------------|
| | 深圳市虹成电子有限公司 | 品名 TITLE | 针座 |
| | | 料号 PART NO | HC-VH-4AW-TW |

| | | | |
|--|---------------|---------------|--------|
| GENERAL TOLERANCES (UNLESS SPECIFIED) | 比列 SCALE | 1:1 | |
| X.X ± 0.35 | X: ± 3.00° | 单位 UNIT | MM |
| X.XX ± 0.25 | X.X: ± 2.00° | 张数 PART NO | 1 OF 1 |
| X.XXX ± 0.15 | X.XX: ± 1.00° | 版本 REV | A |
| | | 审核 CHECKED | 夏操云 |
| | | 批准 APPROVE | 赵亮亮 |

