




UMAX7212401
SFP+ CAGE

MATERIAL (RoHS COMPLIANCE):

CAGE:
COPPER ALLOY


PLATING OPTION 1:
100μ" [2.54 μm] MIN. TIN
PLATING OVER 50 μ" (1.27 μm)
MIN. NICKEL UNDER PLATING.

PLATING OPTION 2:
100μ" [2.54 μm] MIN. NICKEL
PLATING (NOT FOR SOLDER PINS).

DUST COVER
THERMOPLASTIC, COLOR BLACK.


PACKAGING:
TAPE AND REEL OR TRAY PACKAGING.

TEMPERATURE RANGE:
-40°C TO +85°C







M42F-08P-020-P002G
SFP+ CONNECTOR

				.X±0.30	.X°±	APPD: Jason	MAT'L:	DWG NO. C-UMAX7D01117				
				.XX±0.20	.XX°±	CHKD: Schumi	FINISH:		UNITS	SCALE	SHEET	REV
REV	ECN NO.	NAME	DATE	.XXX±0.10	.XXX°±	DRWN:Lei Songping	Q'TY:		MM	1 : 1	1 OF 6	1



FOLDED TABS



REV	ECN NO.	NAME	DATE

TOLERANCE		UMax conn 东莞市友贸实业有限公司 DONGGUAN UMAX ENTERPRISE LIMITED	
LINEAR	ANGLES		
X±0.40	X°± 3°	APPD: Jason	MAT'L:
.X±0.30	.X*±	CHKD: Schumi	FINISH:
.XX±0.20	.XX*±	DRWN: Lei Songping	Q'TY:
.XXX±0.10	.XXX*±		

TITLE: SFP+ CAGE 1x2 NICKEL PLATING Through Hole - Press-Fit		PART NO. UMAX7212401			
		DWG NO. C-UMAX7D01117			
		UNITS	SCALE	SHEET	REV
		MM	1 : 1	2 OF 6	1

CUSTOMER

