







RECOMMENDED OPERATING FLOW:
MATE: 1
UNMATE: 2

				LINEAR	ANGLES	UMax conn 东莞市友贸实业有限公司 DONGGUAN UMAX ENTERPRISE LIMITED		M.2 CONNECTOR 3.2mm H					
C	-----	Terry	Dec,08,2024	X.±0.40	X'±			PART NO.	91302-32-067RXX				
B1	-----	Lei Songping	Sep,02,2019	.X±0.30	.X'±	APPD:	Jason	MAT'L:	DWG NO.	C-91302-32			
B	17017	Terry	Jul,19,2017	.XX±0.20	.XX'±	CHKD:	Schumi	FINISH:		UNITS	SCALE	SHEET	REV
REV	ECN NO.	NAME	DATE	.XXX±0.10	.XXX'±	DRWN:	Terry	Q'TY:		MM	1 : 1	1 OF 5	C

CUSTOMER





DETAIL K
SCALE: 4:1

TOLERANCE		UMax 东莞市友贸实业有限公司 DONGGUAN UMAX ENTERPRISE LIMITED		TITLE: M.2 CONN. GEN4 P=0.5mm 3.2mm H	
LINEAR	ANGLES			PART NO.	91302-32-067RXX
X.±0.40	X'±	APPD:	Jason	MAT'L:	
.X±0.30	.X'±	CHKD:	Schumi	FINISH:	
.XX±0.20	.XX'±	DRWN:	Terry	Q'TY:	
.XXX±0.10	.XXX'±				

REV	SEE SHEET 1	ECN NO.	NAME	DATE	UNITS	SCALE	SHEET	REV
					MM	1 : 1	3 OF 5	C

CUSTOMER

NOTES:

1. MATERIAL :

1.1 HOUSING: THERMOPLASTIC, HIGH TEMPERATURE,
UL94 V-0, COLOR: BLACK.

1.2 CONTACT: COPPER ALLOY.

1.3 FITTING NAIL: COPPER ALLOY.

2. FINISH :

2.1 CONTACT

[SEE TABLE] GOLD PLATING ON THE CONTACT AREA.

GOLD FLASH PLATING ON THE SOLDERING AREA.

1.27um~2.54um [50u"~100u"] MIN. NICKEL UNDERPLATING OVERALL.

2.2 FITTING NAIL

2.54um~5.08um [100u"~200u"] MIN. MATTE-TIN PLATING ON THE SOLDERING AREA.

1.27um~2.54um [50u"~100u"] MIN. NICKEL UNDERPLATING OVERALL.

3. PACKAGING SPEC.: K-91302-401

PART NO.:

91302 - 32 - 067 R X X

32: 3.2mm HEIGHT

67 CONTACTS

PACKING OPTIONS
R: TAPE & REEL


KEY ID OPTIONS
A, B, C, D, E, F
G, H, J, K, L, M

CONTACT AREA PLATING
2: GOLD FLASH
C: 15u" GOLD
D: 30u" GOLD

1.375	1.125	1.5	14.0	2.0	14.0	6.125	M
1.375	1.125	2.5	13.0	3.0	13.0	5.125	L
1.375	1.125	3.5	12.0	4.0	12.0	4.125	K
1.375	1.125	4.5	11.0	5.0	11.0	3.125	J
1.375	1.125	5.5	10.0	6.0	10.0	2.125	H
1.375	1.125	6.5	9.0	7.0	9.0	1.125	G
DIM. G	DIM. F	DIM. E	DIM. D	DIM. C	DIM. B	DIM. A	KEY ID

1.125	1.375	9.5	6.0	9.5	6.5	-1.625	F
1.125	1.375	10.5	5.0	10.5	5.5	-2.625	E
1.125	1.375	11.5	4.0	11.5	4.5	-3.625	D
1.125	1.375	12.5	3.0	12.5	3.5	-4.625	C
1.125	1.375	13.5	2.0	13.5	2.5	-5.625	B
1.125	1.375	14.5	1.0	14.5	1.5	-6.625	A
DIM. G	DIM. F	DIM. E	DIM. D	DIM. C	DIM. B	DIM. A	KEY ID

				TOLERANCE		UMax 东莞市友贸实业有限公司 conn DONGGUAN UMAX ENTERPRISE LIMITED		TITLE: M.2 CONN. GEN4 P=0.5mm 3.2mm H								
				LINEAR	ANGLES			PART NO. 91302-32-067RXX								
				X.±0.40	X'.±											
				.X±0.30	.X'±								APPD: Jason	MAT'L:		DWG NO. C-91302-32
	SEE SHEET 1			.XX±0.20	.XX'±	CHKD: Schumi	FINISH:			UNITS	SCALE	SHEET	REV			
REV	ECN NO.	NAME	DATE	.XXX±0.10	.XXX'±	DRWN: Terry	Q'TY:							MM	1 : 1	



TOLERANCE		UMax 东莞市友贸实业有限公司 conn DONGGUAN UMAX ENTERPRISE LIMITED			TITLE: M.2 CONN. GEN4 P=0.5mm 3.2mm H					
LINEAR	ANGLES				PART NO. 91302-32-067RXX					
X.±0.40	X'.±				DWG NO. C-91302-32					
.X±0.30	.X'±	APPD: Jason	MAT'L:				UNITS	SCALE	SHEET	REV
.XX±0.20	.XX'±	CHKD: Schumi	FINISH:				MM	1 : 1	5 OF 5	C
.XXX±0.10	.XXX'±	DRWN: Terry	Q'TY:							

SEE SHEET 1			
REV	ECN NO.	NAME	DATE