




Pin	DIM A	DIM B	DIM C	DIM D
2	6.00	2.00	4.90	0.80
3	8.00	4.00	6.90	2.80
4	10.00	6.00	8.90	4.80
5	12.00	8.00	10.90	6.80
6	14.00	10.00	12.90	8.80
7	16.00	12.00	14.90	10.80
8	18.00	14.00	16.90	12.80
9	20.00	16.00	18.90	14.80
10	22.00	18.00	20.90	16.80
11	24.00	20.00	22.90	18.80
12	26.00	22.00	24.90	20.80
13	28.00	24.00	26.90	22.80
14	30.00	26.00	28.90	24.80
15	32.00	28.00	30.90	26.80
16	34.00	30.00	32.90	28.80



耐 压: 800V AC/minute

	深圳市虹成电子有限公司		品 名 TITLE		针座	
			料 号 PART NO		HCZZ0256-7	
GENERAL TOLERANCES (UNLESS SPECIFIED)		比 例 SCALE	1 : 1			
X.X ±0.35	X' ±3.00'	单 位 UNIT	MM	制 图 DRAW	AhYe	
X.XX ±0.25	X.X' ±2.00'	张 数 PART NO	1 OF 1	审 核 CHECKED	夏操云	
X.XXX ±0.15	X.XX' ±1.00'	版 本 REV	A	批 准 APPROVE	赵亮亮	