



MTA 156

TE Internal #: 3-644611-2
PCB Mount Header, Vertical, Wire-to-Board, 2 Position, 3.96 mm [.156 in] Centerline, Partially Shrouded, Tin, Through Hole - Solder, Power, MTA 156

[View on TE.com >](#)

Connectors > PCB Connectors > PCB Headers & Receptacles



PCB Connector Assembly Type: **PCB Mount Header**
PCB Mount Orientation: **Vertical**
Connector System: **Wire-to-Board**
Number of Positions: **2**
Number of Rows: **1**

Features

Electrical Characteristics

Operating Voltage	600 VAC
-------------------	---------

Dimensions

Connector Width	10.79 mm[.425 in]
Connector Height	13.84 mm[.545 in]
Connector Length	7.8 mm[.307 in]
PCB Thickness (Recommended)	1.57 mm[.062 in]

Packaging Features

Packaging Quantity	500
Packaging Method	Bag

Industry Standards

Compatible With Agency/Standards Products	UL, CSA
UL Rating	Recognized
Compatible With Approved Standards Products	UL E28476
Glow Wire Rating	Standard Part - Not Glow Wire



UL Flammability Rating	UL 94V-0
------------------------	----------

Usage Conditions

Operating Temperature (Max)	105 °C[221 °F]
Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]

Mechanical Attachment

Panel Mount Feature	Without
Mating Retention Type	Polarized Lock
Mating Retention	With
PCB Mount Retention	Without
PCB Mount Alignment	Without
Connector Mounting Type	Board Mount
Mating Alignment	Without

Termination Features

Square Termination Post & Tail Dimension	1.14 mm[.045 in]
Termination Post & Tail Length	3.18 mm[.125 in]
Termination Method to PCB	Through Hole - Solder

Contact Features

Contact Underplating Material	Nickel
Contact Underplating Material Thickness	1.27 µm[50 µin]
Contact Size	1.14mm
Contact Mating Area Plating Material Thickness	3.81 – 8.89 µm[150 – 350 µin]
Mating Square Post Dimension	1.14 mm[.045 in]
Contact Base Material	Copper Alloy
PCB Contact Termination Area Plating Material	Tin
Contact Mating Area Plating Material Finish	Matte
PCB Contact Termination Area Plating Material Finish	Matte
Contact Shape & Form	Square
PCB Contact Termination Area Plating Material Thickness	3.81 – 8.89 µm[150 – 350 µin]
Contact Layout	Inline
Contact Mating Area Length	11.43 mm[.45 in]
Contact Mating Area Plating Material	Tin
Contact Type	Tab



Contact Current Rating (Max)	14.24 A
------------------------------	---------

Housing Features

Mating Entry Location	Top
Housing Material	Thermoplastic Polyester - Glass-Filled
Centerline (Pitch)	3.96 mm[.156 in]

Configuration Features

Connector Contact Load Condition	Fully Loaded
Number of Columns	2
Number of Loaded Positions	2
Keying & Polarized Position Locations	None
Number of Power Positions	2
PCB Mount Orientation	Vertical
Number of Positions	2
Number of Rows	1

Product Type Features

Mixed & Hybrid Header	No
Connector Shape	Rectangular
PCB Connector Assembly Type	PCB Mount Header
Connector System	Wire-to-Board
Header Type	Partially Shrouded
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board

Body Features

Primary Product Color	Natural
-----------------------	---------

Operation/Application

Circuit Application	Power
---------------------	-------

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)




EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JAN 2024 (240) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 3-644467-2
02P MTA156 CONN ASSY 22AWG LF



TE Part # 643067-2
02P MTA156 MOLDED COVER



TE Part # 3-644464-2
02P MTA156 CONN ASSY 24AWG LF



TE Part # 3-644465-2
02P MTA156 CONN ASSY 18AWG ORA



TE Part # 3-644462-2
02P MTA156 CONN ASSY 20AWG LF



TE Part # 3-640429-2
02P MTA156 CONN ASSY 24AWG WHT




TE Part # 3-640435-2
02P MTA156 CONN ASSY 26AWG LF




TE Part # 3-643817-2
02P MTA156 CONN ASSY 18AWG ORA







TE Part # 3-643821-2
02P MTA156 CONN ASSY 26AWG LF




TE Part # 640251-2
02P SL156 HSG W/O RAMP NATL




TE Part # 3-640605-2
02P MTA156 CONN ASSY 20AWG LF



TE Part # 3-640430-2
02P MTA156 CONN ASSY 26AWG BLU



TE Part # 3-643818-2
02P MTA156 CONN ASSY 20AWG YEL




TE Part # 643071-2
02P MTA156 FD-THRU COVER




TE Part # 3-640599-2
02P MTA156 CONN ASSY 18AWG ORA




TE Part # 3-644461-2
02P MTA156 CONN ASSY 18AWG LF



TE Part # 3-644466-2
02P MTA156 CONN ASSY 20AWG YEL



TE Part # 3-640434-2
02P MTA156 CONN ASSY 24AWG WHT



TE Part # 3-640427-2
02P MTA156 CONN ASSY 20AWG YEL



TE Part # 3-640433-2
02P MTA156 CONN ASSY 22AWG RED

Also in the Series | **MTA 156**



Connector Caps & Covers(89)



Connector Contacts(4)




Connector Hardware(2)




Power Contacts(3)



Rectangular Power Connectors(331)



Standard Rectangular Connectors(336)



Wire-to-Board Headers & Receptacles (677)

Customers Also Bought



TE Part #323008
PIDG R 22-16 COMM 22-18 MIL 6



TE Part #1-1618002-8
EV200HAANA=RELAY, SPST-NO WITH



TE Part #770988-3
MINI UMNL SOK 22-18AWG AU LP




TE Part #6-1676481-7
CPF 0603 3K9 0.1% 25PPM 1K RL




TE Part #5-146280-3
03 MODII HDR SRST B/A .100CL




TE Part #1624352-1
NTC0805 5% 220R




TE Part #2118059-1
WIMAX SINGLE BAND PCB Antenna



TE Part #ZPF000000000098400
164-8013-08 A499



TE Part #M3041-000006-500PG
PRESS XDCR M3041-000006-500PG



TE Part #20007265-00
PRESS XDCR US342-000002-050PA

Documents

Product Drawings

02P MTA156 HDR POL WO PEGS LF

English

CAD Files

Customer View Model

ENG_CVM_3-644611-2_H1.2d_dxf.zip

English

3D PDF

English

Customer View Model

ENG_CVM_3-644611-2_H1.3d_igs.zip

English

Customer View Model

ENG_CVM_3-644611-2_H1.3d_stp.zip

English

3D PDF

3D



Customer View Model

[ENG_CVM_CVM_3-644611-2_F.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_3-644611-2_F.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_3-644611-2_F.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Application Specification](#)

English