




Connectors > Socket Connectors > Memory Sockets > SO DIMM Sockets > DDR3 SO DIMM Sockets



DRAM Type: **Small Outline (SO)**
Stack Height: **5.6 mm [.22 in]**
Module Orientation: **Right Angle**
Number of Positions: **144**
Centerline (Pitch): **.8 mm [.031 in]**

[All DDR3 SO DIMM Sockets \(12\)](#)

Features

Electrical Characteristics

DRAM Voltage	3.3 V
--------------	-------

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Termination Features

Insertion Style	Cam-In
Termination Method to PCB	Surface Mount

Mechanical Attachment

Connector Mounting Type	Board Mount
PCB Mount Retention Type	Hold-Down Post
Mating Alignment Type	Offset Left
PCB Mount Retention	With

Packaging Features

Packaging Quantity	12
Packaging Method	Box

Contact Features

Memory Socket Type	Memory Card
--------------------	-------------



Contact Base Material	Copper Alloy
PCB Contact Termination Area Plating Material	Gold Flash
Contact Mating Area Plating Material	Gold
Contact Mating Area Plating Material Thickness	.25 µm[9.84 µin]

Body Features

Latch Plating Material	Tin
Latch Material	Stainless Steel
Module Key Type	SDRAM
Ejector Location	None
Connector Profile	High

Housing Features

Housing Material	High Temperature Plastic
Housing Color	Natural
Centerline (Pitch)	.8 mm[.031 in]

Configuration Features

Number of Bays	2
Number of Keys	1
Number of Rows	2
Module Orientation	Right Angle
Number of Positions	144

Product Type Features

Connector & Contact Terminates To	Printed Circuit Board
Connector System	Cable-to-Board
DRAM Type	Small Outline (SO)

Dimensions

Stack Height	5.6 mm[.22 in]
Row-to-Row Spacing	6.2 mm[.244 in]

Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Signal
---------------------	--------

Other



EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 260°C


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts




Also in the Series | AMP-METRIMATE




Card Edge Power Connectors(1)



Connector Hardware(1)



PCB Headers & Receptacles(8)




Rack & Panel Connectors(1)



Rectangular Power Connectors(2)



SO DIMM Sockets(12)



Wire-to-Board Headers & Receptacles (2)

Customers Also Bought




TE Part #3-1419104-6
T9ASSD22-24



TE Part #2-644486-2
02P MTA100 SHRDED HDR ASSY SN



TE Part #2041376-2
RJ45 W LED 2X2,30u",DIP,H=25.4mm




TE Part #87499-8
04 MODIV HSG COMP SR .100CL



TE Part #3-1625890-2
2W SM M/OX 5% 22K



TE Part #2842103-2
2P,2MM,BRK HDR,SRVT,SMD,0.38AU, TR W/CAP



TE Part #8-1879744-6
RP 1J 392R 0.1% 15PPM CUT LENGTH



TE Part #1-5161390-0
10P.DIP SWITCH ASSY



TE Part #1-338088-3
8/8 INV.MOD.JACK



TE Part #203543-E
MJ HS VG * 8 8 4 * * * 999999 30 3/4 J 3

Documents



Product Drawings

SKT,SODIMM,144P,SDRAM3.3V,HIGH

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_3-390112-1_AB.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_3-390112-1_AB.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_3-390112-1_AB.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English