




PRODUCT NUMBER: 6857-0-15-01-47-01-10-0

www.mill-max.com
DATA SHEET



6857-0-15-01-47-01-10-0 SPECIFICATIONS



General Info		Materials	Technical Specs
Description ¹ :	Receptacle With No Tail	Shell Material ³ : Brass Alloy	Mechanical life 1,000 Cycles Minimum (Durability) ⁶ :
Mounting Feature:	Press-Fit into a Non-Plated Through Hole (NPTH)	Shell Plating ⁴ : 200 - 300 μ " Tin/Lead over Nickel	Operating Temperature Range ⁷ : -55/+125° C
Mounting Hole:	.062" (1,575mm)	Contact Plating ⁵ : 200 - 300 μ " Tin/Lead over Nickel	Current Rating ⁸ : 4.5A @ 10°C Temperature Rise
Pin Diameter Range:	.025"-.037" (0,635-0,940mm)		Contact Resistance ⁹ : 10 m Ω Max
Packaging:	Packaged in Bulk		Shock ¹⁰ : No Elect. Discontinuity > 1 μ s @ 50g
RoHS:	No		Vibration ¹¹ : No Elect. Discontinuity > 1 μ s @ 10-2000HZ, 20 G
Product Lifecycle ² :	Active		

NOTES:

1. Standard Tolerances:
Lengths +/- .005" (0,13)
Diameters: +/- .002" (0,051)
Angles: +/- 2°
2. Part is Active and in Production, No Scheduled Obsolescence
3. Brass Alloy 360 per ASTM B 16, or 385 per ASTM B455
4. TIN/LEAD (93/7) per ASTM B 545 (Appendix X6.3.2.5 to eliminate whisker growth) Bright finish; NICKEL per ASTM B 689, Type 2 (Bright)
5. TIN/LEAD (93/7) per ASTM B 545 (Appendix X6.3.2.5 to eliminate whisker growth) Bright finish, NICKEL per ASTM B 689, Type 2 (Bright)
6. Receptacles are capable of 1,000 Minimum insertion/extraction cycles for a broad range of applications. Mating pin size, shape and finish, along with application specific variables, will affect the life of a receptacle contact.
7. Per IEC 60512-11-(4,9,10,12)
8. Per IEC 60512-5-1, Current Carrying Capacity (evaluated at 10° C Temp. Rise)
9. Per EIA-364-23C, Low Level Contact Resistance
10. Per IEC 60512-6-3: Test 6c: Shock
11. Per IEC 60512-6-4: Test 6d: Vibration (sinusoidal)

CONTACT:

#47 CONTACT FOR .025"-.037" DIA. & .025" SQ. ($\delta = .011$) 6-FINGER (BeCu), GROUP D



The insertion / extraction force characteristics above were derived using a 30 microinch gold-plated contact and polished steel gauge pins having a bullet-shaped tip.

The curves represent typical average values; they are best used to compare the differences between similar size contacts and to guide you in selecting one that is suitable for your application. Your results may vary, so for your specification, we encourage you to obtain complimentary samples for your evaluation.

Material	Beryllium Copper	Fingers	6
Length	.080" (2,032mm)	Maximum Current	15A @ 30° C Temp. Rise
Maximum Operating Temp @ Max Current	120.00° C	20% De-rated Maximum Current	12.00A
Contact Resistance	10.00mΩ Max	Contact Group	D

ADDITIONAL NOTES AND SPECIFICATIONS

In the interest of improved design, quality and performance , Mill-Max reserves the right to make changes in its specifications without prior notice. Specifications and tolerances are provided wherever possible. The tolerance on dimensions of critical to function features is typically held tighter than the stated standard tolerances, such as press-fits, holes and lengths affecting the coplanarity of SMT products. Due to the wide variety of interconnects Mill-Max offers, the specific tolerances vary from product to product. If you need information regarding the tolerance of a particular part, please contact Technical Services.

RELATED LINKS AND DOCUMENTS

Engineering Notebook: (<https://www.mill-max.com/engineering-notebooks/introduction-to-mill-max-press-fit-technology>)

Environmental Compliance: (<https://www.mill-max.com/rohs>)