

NOTES:

1. MATERIAL:

1.1 HOUSING: THERMOPLASTIC, HIGH TEMP, UL94V-0, COLOR: SEE PART No..

1.2 CONTACTS: COPPER ALLOY.

1.3 PAD: COPPER ALLOY.

1.4 CAP: THERMOPLASTIC, HIGH TEMP, UL94V-0, COLOR: BLACK.

2. FINISH:

2.1 CONTACT:

SELECTIVE GOLD PLATING ON THE CONTACT AREA.

100 μ " MIN. MATTE-TIN PLATING ON THE SOLDER TAILS,50 μ " MIN. NICKEL UNDERPLATING OVERALL.

2.2 PAD:

100 μ " MIN. MATTE-TIN PLATING WITH 50 μ " MIN. NICKEL UNDERPLATE OVERALL.

3. PRODUCT SPEC: PS-GEN5-01.

4. PACKAGING SPEC: 311304001 FOR TRAY, 311304002 FOR TAPE & REEL, 311304003 FOR HARD TRAY.

PART NO.

91650 - X 1 X X X HF

Ridge Options

0: Non Ridge

1: With Ridge

HSG Color

1: Black

Post Options

0: With Post

1: Without Post

Contact Plating

0: 30 μ " Au1: 15 μ " Au

2: Gold Flash

Packing Options

T: Tray Packaging

C: Tray Packaging With Cap

N: Tray Packaging With Mylar

R: Tape & Reel Packaging (20PH)

P: Tape & Reel Packaging With Cap (20PH)

Q: Tape & Reel Packaging With Cap (24PH)

M: Tape & Reel Packaging With Mylar (20PH)

J: Tape & Reel Packaging With Mylar (24PH)

Y: Hard Tray (338x235)

Z: Hard Tray (338x235) With Mylar

B: Hard Tray (338x235) With Cap


No. of Pins

0: 36P


1: 64P

2: 98P


3: 164P




WITH CAP



WITH MYLAR



WITH RIDGE



NON RIDGE

REV	SEE SHEET 1	NAME	DATE	.XX±0.20	.XX'±	CHKD: Schumi	FINISH:	UNITS	SCALE	SHEET	REV
1	ECN NO.	3	4	.XXX±0.10	.XXX'±	DRWN: Lei Songping	Q'TY:	MM	1 : 1	3 OF 4	5

TOLERANCE		UMax conn 东莞市友贸实业有限公司 DONGGUAN UMAX ENTERPRISE LIMITED	TITLE: PCI-E CARD EDGE GEN5 SMT								
LINEAR	ANGLES		PART NO. 91650-XXXXXX								
X.±0.40	X'.±		DWG NO. C-91650								
.X±0.30	.X'±	APPD: Jason	MAT'L:								
.XX±0.20	.XX'±	CHKD: Schumi	FINISH:								
.XXX±0.10	.XXX'±	DRWN: Lei Songping	Q'TY:								

CUSTOMER

