

LR1F620R

✓ ACTIVE

Neohm | Neohm LR

TE Internal #: 1622539-1

Through-Hole General Purpose Resistor, Thin Film, .6 W, 620 ohm,
1 %, ±50 ppm/°C, Axial-Leaded, Copper Termination, 6.2 x 2.3 mm,
Neohm LR

[View on TE.com >](#)



Passive Components > Resistors > Through-Hole Resistors



Resistor Type: **General Purpose Resistor**
Element Type: **Thin Film**
Power Rating: **.6 W**
Resistance Class: **Up to 1kΩ**
Resistance Value: **620 Ω**

Features

Usage Conditions

Operating Temperature Range	-55 – 155 °C
Temperature Coefficient	±50 ppm/°C

Electrical Characteristics

Operating Voltage	350 V
Power Rating	.6 W
Resistance Class	Up to 1kΩ
Resistance Value	620 Ω
Passive Component Tolerance	1 %

Product Type Features

Resistor Type	General Purpose Resistor
Element Type	Thin Film

Configuration Features

Number of Resistors	1
---------------------	---

Body Features

Lead Type	Axial-Leaded
-----------	--------------

Termination Features

Termination Area Base Material	Copper
Number of Terminations	2



Dimensions

Passive Component Dimensions	6.2 x 2.3 mm
------------------------------	--------------

Packaging Features

Packaging Method	Ammo Packed
------------------	-------------

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUL 2021 (219) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

LR1F620R

Through-Hole General Purpose Resistor, Thin Film, .6 W, 620 ohm, 1 %, ±50 ppm/°C, Axial-Leaded, Copper Termination, 6.2 x 2.3 mm, Neohm LR



TE Part # 1622598-1
LR1L 5% R10



TE Part # 1622742-1
LR2 1% 39K



TE Part # 1614978-1
LR0204 1% 10K



TE Part # 1622367-1
LR1 1% 1M0



TE Part # 1622298-1
LR1 1% 10K

Also in the Series | Neohm LR



DIMM Sockets(5)



Through-Hole Resistors(490)

Customers Also Bought




TE Part #CSA-RPSM-216-SAFB
SMA to RP-SMA 216mm RG174



TE Part #6-1879501-1
CRGH2512 5% 330R 2W




TE Part #86BSD150PA-3AIC
150 PSIA 14 BIT DIGITAL PRESSURE SENSOR




TE Part #3103413002
55A0112-24-8



TE Part #AS210-35PB
RECEPT.BOX MNTG.TYPE 2





TE Part #1630018-3
R2164M01 16K5 1%



TE Part #86455-000
FFCS-05 FLOW SWITCH



TE Part #CQ93033001
FLDWC0311-1.00-0CK0202/1



Documents

Product Drawings

LR1 1% 620R

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1622539-1_BA.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1622539-1_BA.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1622539-1_BA.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

1309350_PASSIVE_COMPONENT

English

Metal Film Fixed Resistors - Type LR series

English