




Terminals & Splices > Magnet Wire Terminals



Magnet Wire Terminal Type: **Tab**
Mating Tab Width: **6.35 mm [.25 in]**
Mating Tab Thickness: **.81 mm [.032 in]**
Magnet Wire Size: **.16 – 1.02 mm**

Features

Usage Conditions

Insulation Option	Uninsulated
-------------------	-------------

Packaging Features

Packaging Quantity	2000
Packaging Method	Reel

Dimensions

Terminal Height	8.38 mm[.33 in]
Magnet Wire Size	.16 – 1.02 mm
Stock Thickness (Magnet Wire Side)	.51 mm[.02 in]
Product Length	18.92 mm[.745 in]

Product Type Features

Compatible With Discrete Wire Type	Solid, Magnet Wire
------------------------------------	--------------------

Contact Features

Magnet Wire Terminal Type	Tab
Mating Tab Width	6.35 mm[.25 in]



Mating Tab Thickness	.81 mm[.032 in]
Terminal Plating Material	Tin
Terminal Orientation	Straight

Termination Features

Termination Method to Wire & Cable	Insulation Displacement (IDC)
------------------------------------	-------------------------------

Mechanical Attachment

Mating Retention Type	Hole, Barbs
-----------------------	-------------

Operation/Application

Compatible With Wire Base Material	Copper
------------------------------------	--------

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>




EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>




Compatible Parts

 TE Part # 2-284937-1 TAB SIAMEZE CONTACT .250" x.03	 TE Part # 1601040-1 SIAMEZE TERMINALS	 TE Part # 1601035-2 TAB,187X032,STD,SMZ	 TE Part # 1-1601061-2 TAB,250X032,STD,SMZ
 TE Part # 2-1601139-2 TAB,250 X 032,MED,SMZ	 TE Part # 4-1601110-2 131-181-014=TAB,1.2X.81,STD,SMZ	 TE Part # 3-1601061-2 TAB,250X032,STD,SMZ	 TE Part # 2348504-2 STD RANGE WIRE TO .250 X .032 TAB SMZ
 TE Part # 1601425 531-007-000=POCKET SPECIFICATION	 TE Part # 2-1601121-2 TAB PAIR,1.50X0.81,FINESMZ	 TE Part # 293231-1 MULTI BARB SIAMEZE TERMINAL STD RANGE	 TE Part # 2-1601003-1 131-005-000=TAB,250X032,STD,SMZ


Also in the Series | SIAMEZE

 Insertion & Extraction Tools(1)	 Magnet Wire Terminals(191)
--	---


Customers Also Bought




TE Part #776428-3
[AS16,CAP ASSY,ST,02P,N SEAL,CODE C](#)



TE Part #794954-4
[4P RCPT VAL-U-LOK V2](#)



TE Part #1217080-1
[FASTON 205/250 PCB MOUNTED TPBR](#)



TE Part #2-1601002-2
[131-004-002=TAB,250X032,STDSMZ](#)



TE Part #968875-000
[DWP-125-1/4-0-1.25IN](#)



TE Part #638112-1
[PIN, SF, SIZE 16, 14-18 AWG,NO INS, AU/SN](#)



TE Part #4-2209520-5
[46POS,MCON 1.2,REC HSG ASSY,SLD](#)

TE Part #1601063-4
[TAB,059X032,STDSMZ](#)

TE Part #2386572-2

TE Part #2386575-2

Documents

Product Drawings

[131-055-002=TAB,250X032,STDSMZ](#)

English

[131-055-002=TAB,250X032,STDSMZ](#)

English

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_1601002-2_G.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1601002-2_G.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1601002-2_G.3d_stp.zip](#)

English



Customer View Model

[ENG_CVM_1601002-2_D2.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_1601002-2_D2.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_1601002-2_D2.2d_dxf.zip](#)

English

3D PDF

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[1654742_HOUSEHOLD_APPLIANCES_RAST5](#)

English

Magnet Wire Terminals & Splices

English

[1-1773702-7 _IDC_Magnet_Wire](#)

English

Product Specifications

[Application Specification](#)

English

Agency Approvals

[UL Report](#)

English