

[Connectors > Terminal Blocks & Strips > Barrier Strips](#)

Number of Positions: 4

Barrier Strip Style: Dual Barrier

Bottom Termination Type: Printed Circuit Pin

Connector System: Wire-to-Board

Centerline (Pitch): 9.53 mm [.375 in]

Features

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features

Packaging Method	Package
------------------	---------

Packaging Quantity	45
--------------------	----

Operation/Application

Circuit Application	Power
---------------------	-------

Mechanical Attachment

Top Termination Type	Wire Clamp Combo Head
----------------------	-----------------------

Mounting Options	None
------------------	------

Screw Plating Material	Zinc
------------------------	------

Screw Material	Steel
----------------	-------

Thread Size	6-32
-------------	------

Screw Head Type	Wire Clamp Combo Head
-----------------	-----------------------

Connector Mounting Type	Board Mount
-------------------------	-------------

Contact Features

Contact Base Material	Copper Alloy
PCB Contact Termination Area Plating Material	Tin
Contact Current Rating (Max)	20 A

Dimensions

Product Length	39.65 mm[1.561 in]
Wire Size	22 – 12 AWG

Housing Features

Housing Material	Polyamide
Centerline (Pitch)	9.53 mm[.375 in]

Product Type Features

Block Style	Flat Bottom with standoffs
Connector System	Wire-to-Board
Connector & Contact Terminates To	Printed Circuit Board

Body Features

Terminal Profile	Low
Primary Product Color	Black
Product Orientation	Vertical
Barrier Strip Style	Dual Barrier

Configuration Features

Number of Levels	1
Number of Positions	4
Number of Rows	1

Termination Features

Bottom Termination Type	Printed Circuit Pin
-------------------------	---------------------

Electrical Characteristics

Operating Voltage	300 V
-------------------	-------

Usage Conditions

Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]
-----------------------------	----------------------------

Other

EU RoHS Compliance	Compliant
--------------------	-----------

EU ELV Compliance

Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # 6-1437664-2
NC6-P106-04=NC6 ASSEMBLY

Also in the Series | Buchanan NC6



Barrier Strips(30)

Customers Also Bought

TE Part #8-1879233-1
SMW5 220R 5%TE Part #35184
TERMINAL,SOLIS R 2 3/8TE Part #4-1437664-1
NC6-P108-08=NC6 ASSEMBLYTE Part #1-1393771-6
JWD-171-24=REED RELAYSTE Part #2118909-2
PCB Ant, MHF, 268.8mm, Wi-Fi 6E
TripleTE Part #4-1609967-5
KEM 25A 1S HIGH PER SP DELTA
520VACTE Part #1888946-1
CONNECTOR ASSEMBLY, SEC II
POWER, DUAL PTE Part #C17298-000
WP-381064-10-9TE Part #3-1437653-8
6PCV-10-1193=6PCV SPECIALTE Part #7218310001
RPS-2.5K-18-12/2.0-S1-9

Documents

Product Drawings

[NC6-P108-04=7180XX002/30](#)

English

CAD Files

Customer View Model

[ENG_CVM_CVM_3-1437664-3_M1.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_CVM_3-1437664-3_M1.2d_dxf.zip](#)

English

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_3-1437664-3_M1.3d_jgs.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[BUCHANAN TERMINAL BLOCKS CATALOG - BARRIER STRIPS](#)

English

[1-1773458-2_BARRIER_STRIPS_QUICK_REFERENCE_GUIDE](#)

English

Agency Approvals

[UL](#)

English