

3-2158000-1

✓ ACTIVE

SCHRACK | SCHRACK Power PCB Relay RZ

TE Internal #: 3-2158000-1

General Purpose Power Relay, DC, Monostable, 1 Form C SPDT-CO, 16 A Contact Rating, 24 VDC Coil Voltage, SCHRACK Power PCB Relay RZ

[View on TE.com >](#)

Relays & Contactors > Electromechanical Relays > PCB Power Relay: 12-16 Amp, Monostable

Relay & Contactor Type: **General Purpose Power Relay**Current Type: **DC**Coil Magnetic System: **Monostable**Contact Arrangement: **1 Form C SPDT-CO**Contact Current Rating: **16 A**[All PCB Power Relay: 12-16 Amp, Monostable \(75\)](#)

Features

Contact Features

Contact Material	AgSnO
------------------	-------

Dimensions

Insulation Clearance Between Contact & Coil	10 mm
Insulation Creepage Between Contact & Coil	10 mm
Product Width	12.7 mm[.5 in]
Product Length	29 mm[1.14 in]
Product Height	15.7 mm[.618 in]

Packaging Features

Packaging Method	Box & Tube
------------------	------------

Other

Coil Power Rating Class	.4 – .5 W
Contact Current Class	16 A
Environmental Ambient Temperature Class	-40 – 85 °C
Height Class (Mechanical)	15 – 16 mm
Length Class (Mechanical)	25 – 30 mm
Width Class (Mechanical)	12 – 16 mm
EU RoHS Compliance	Compliant

EU ELV Compliance	Compliant
-------------------	-----------

Usage Conditions

Environmental Category of Protection	RTII
Environmental Ambient Temperature (Max)	85 °C[185 °F]

Electrical Characteristics

Contact Limiting Short-Time Current	30 A
Contact Limiting Making Current	16 A
Contact Limiting Continuous Current	16 A
Contact Limiting Breaking Current	16 A
Insulation Initial Dielectric Between Open Contacts	1000 Vrms
Contact Switching Voltage (Max)	277 VAC
Contact Switching Load (Min)	100mA @ 12V
Coil Resistance	1440 Ω
Contact Current Rating	16 A
Coil Voltage Rating	24 VDC
Contact Voltage Rating	250 VDC
Coil Power Rating DC	.4 W
Insulation Initial Dielectric Between Contacts & Coil	5000 Vrms

Configuration Features

Contact Number of Poles	1
Contact Arrangement	1 Form C SPDT-CO

Operation/Application

Solder Process	Wave Solder
Current Type	DC
Coil Magnetic System	Monostable

Product Type Features

Relay & Contactor Type	General Purpose Power Relay
------------------------	-----------------------------

Body Features

Enclosure Type	Flux Resistant Automatic Soldering
----------------	------------------------------------

Termination Features

Main Termination & Connection Type	Solder Pins
Coil Termination & Connection Type	Solder Pins

Mechanical Attachment

Product Mount Type

Board Mount

Product Compliance

For compliance documentation, visit the product page on [TE.com](https://te.com)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # 5-1415899-5
RZ03-1C3-D024


Also in the Series | [SCHRACK Power PCB Relay RZ](#)



DC Relays(83)





General Purpose Power Relays(83)



PCB Relays(83)

Customers Also Bought

TE Part #338068-4
MICRO-MATCH FTE, 4PTE Part #292173-3
CT BOX HDR H SMT 3P O/TAPE BLATE Part #1-1825027-1
FSMRA4JH04=R/A,TACT PB SW,160GTE Part #1-1586041-4
14P VAL-U-LOK R/A HDR V2TE Part #1-87756-8
MOD IV RECP LPTE Part #2267075-1
PMS9P1B08M2RETE Part #1-1437559-8
MTG206N=SWITCH TOG MUSTANGTE Part #1825100-1
TPF11CGPC004TE Part #8-1437627-2
G12B=BUTTON GUARD BLACKTE Part #5-1814400-2
SMA R/A PCB Skt GZD

Documents

CAD Files

Customer View Model

[ENG_CVM_CVM_3-2158000-1_C.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_3-2158000-1_C.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_CVM_3-2158000-1_C.2d_dxf.zip](#)

English

[3D PDF](#)

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[Power PCB Relay RZ Datasheet](#)

English

Product Specifications

[Definitions General Purpose Relays](#)

English

Agency Approvals

[VDE Certificate](#)

English