




MAG-MATE

TE Internal #: 1742633-1
Tab, 1.65 mm [.065 in] Tab Width, .04 mm Magnet Wire, 31 AWG
Magnet Wire, Insulation Displacement (IDC), Tin Plating, MAG-MATE, Magnet Wire Terminals

[View on TE.com >](#)

Terminals & Splices > Magnet Wire Terminals



Magnet Wire Terminal Type: **Tab**
Mating Tab Width: **1.65 mm [.065 in]**
Mating Tab Thickness: **.5 mm [.02 in]**
Magnet Wire Size: **.04 mm**

Features

Usage Conditions

Insulation Option	Uninsulated
-------------------	-------------

Dimensions

Terminal Height	.87 mm[.03 in]
Magnet Wire Size	.04 mm
Stock Thickness (Magnet Wire Side)	.51 mm[.02 in]
Product Length	22.09 mm[.87 in]

Product Type Features

Compatible With Discrete Wire Type	Solid, Magnet Wire
------------------------------------	--------------------

Contact Features

Magnet Wire Terminal Type	Tab
Mating Tab Width	1.65 mm[.065 in]
Mating Tab Thickness	.5 mm[.02 in]
Terminal Plating Material	Tin
Terminal Orientation	Straight



Termination Features

Termination Method to Wire & Cable	Insulation Displacement (IDC)
------------------------------------	-------------------------------

Mechanical Attachment

Mating Retention Type	Barbs
-----------------------	-------

Operation/Application

Compatible With Wire Base Material	Copper
------------------------------------	--------

Packaging Features

Packaging Method	Reel
------------------	------

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts

TE Part # 2238088-1
MAG-MATE TAB 33-31 CU / 31-29 AL TPBR

TE Part # 1217491-1
TAB FASTON 187 500 BOX MAGMATE

TE Part # 1742242-1
TAB,187 FASTON,LP,MAG-MATE

TE Part # 1742858-1
TAB, PLAIN, 187 MAG-MATE SLIM

TE Part # 1742160-1
TAB,187 FASTON,MAG-MATE

TE Part # 1987199-1
BRIDGE CONTACT

TE Part # 1742857-1
TAB, PLAIN, 187 MAG-MATE SLIM

Also in the Series | MAG-MATE

Insertion & Extraction Tools(6)

Magnet Wire Terminals(329)

PCB Terminals(1)

Customers Also Bought

TE Part #CAT-H3399-CH8172
Heavy Duty Sealed Connector Series Housings

TE Part #1670365-1
COVER MIXED,180,2-3POS,BK

TE Part #963531-2
PLUG FOR CAVITY DIA3,6MM

Documents

- CAD Files
- 3D PDF
- 3D
- Customer View Model
- ENG_CVM_CVM_1742633-1_B.2d_dxf.zip

1742633-1

Tab, 1.65 mm [.065 in] Tab Width, .04 mm Magnet Wire, 31 AWG Magnet Wire, Insulation Displacement (IDC), Tin Plating, MAG-MATE, Magnet Wire Terminals



English

Customer View Model

[ENG_CVM_CVM_1742633-1_B.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1742633-1_B.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[Magnet Wire Terminals & Splices](#)

English

Product Specifications

[Application Specification](#)

English