




Connectors > PCB Connectors > Card Edge Connectors > Standard Edge Connectors



Connector System: **Wire-to-Board**
Number of Positions: **7**
Centerline (Pitch): **5 mm [.196 in]**
Termination Method to Wire & Cable: **Insulation Displacement (IDC)**
Number of Rows: **1**

Features

Electrical Characteristics

Operating Voltage	220 VDC
-------------------	---------

Industry Standards

Compatible With Agency/Standards Products	UL
UL Flammability Rating	UL 94V-2

Packaging Features

Packaging Method	Tray
Packaging Quantity	455

Dimensions

Compatible Insulation Diameter Range	2 – 2.8 mm[.078 – .11 in]
Wire Size	20 – 18 AWG

Mechanical Attachment

Mating Alignment Type	Polarizing Slot
Mating Alignment	With



Connector Mounting Type	Cable Mount (Free-Hanging)
-------------------------	----------------------------

Contact Features

PCB Contact Termination Area Plating Material Thickness	2 μm[78.74 μin]
Contact Mating Area Plating Material	Tin
Contact Base Material	Brass
PCB Contact Termination Area Plating Material	Tin
Contact Type	Receptacle
Contact Mating Area Plating Material Thickness	2 μm[78.74 μin]
Contact Current Rating (Max)	6 A

Configuration Features

Card Entry Style	Side
Number of Positions	7
Number of Rows	1
Connector Contact Load Condition	Fully Loaded

Product Type Features

Connector System	Wire-to-Board
Connector & Housing Type	Receptacle
Connector & Contact Terminates To	Wire & Cable

Body Features

Primary Product Color	Natural
-----------------------	---------

Termination Features

Termination Method to Wire & Cable	Insulation Displacement (IDC)
------------------------------------	-------------------------------

Housing Features

Centerline (Pitch)	5 mm[.196 in]
Housing Material	Polyamide 6.6 GF

Usage Conditions

Operating Temperature Range	-25 – 105 °C[-13 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power
---------------------	-------

Other

EU RoHS Compliance	Compliant
--------------------	-----------



EU ELV Compliance

Compliant

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1-282049-1
AMP MONO-SHAPE P.C.B.CONN9P.
GL



TE Part # 1-282042-1
AMP MONO-SHAPE P.C.B.CONN2P.
GL



TE Part # 1-282042-5
AMP MONO-SHAPE P.C.B.CONN2P.
GL



TE Part # 1-282046-1
AMP MONO-SHAPE P.C.B.CONN6P.
GL





TE Part # 1-282043-2
AMP MONO-SHAPE P.C.B.CONN3P. GL



TE Part # 1-282045-1
AMP MONO-SHAPE P.C.B.CONN5P. G



TE Part # 1-284561-2
MONO SHAPE MK I 2 POS PCB CONN.S ASS'Y



TE Part # 1-282044-1
AMP MONO-SHAPE P.C.B.CONN4P. G



TE Part # 1-282050-1
AMP MONO-SHAPE P.C.B.CONN10P. G

Also in the Series | RAST 5 IDC Connectors



Automotive Terminals(8)




Connector Contacts(14)



Power Contacts(5)



Rectangular Connector Housings(1)



Standard Edge Connectors(31)



Standard Rectangular Connectors(63)

Customers Also Bought



TE Part #1-282003-2
AMP MONO-SHAPE TAB CONN 3P. GL




TE Part #1-282002-6
MONO-SHAPE MK I TAB CONN ASSY



TE Part #1-282002-3
AMP MONO-SHAPE TAB CONN 2P. G



TE Part #1-282002-4
MONO-SHAPE MK I CONN. ASSY TAB 2P



TE Part #1-282003-6
AMP MONO-SHAPE TAB CONN



TE Part #3-1534798-5
AMP DUOPLUG MK2 CONNECTOR
5P SELECTIVE



TE Part #284865-5
Direct mount card edge conn.,



TE Part #284970-3
Duoplug Std 3 pos. reinf. cover



TE Part #2-284931-5
DUOPLUG Standard, female conn.



TE Part #2-284932-5
DUOPLUG STD FEMALE CONN., 5
POS.

Documents

CAD Files

Customer View Model

ENG_CVM_CVM_1-282047-1_U.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-282047-1_U.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1-282047-1_U.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

RAST Connector System Catalog

English

Product Specifications

Application Specification

English

Agency Approvals

VDE Certificate

English