




Connectors > PCB Connectors > Backplane Connectors > Eurocard Connectors



Connector & Housing Type: **Receptacle**  
Connector System: **Board-to-Board**  
Termination Post & Tail Length: **3.3 mm [.13 in]**  
Number of Positions: **144**  
Centerline (Pitch): **2.54 mm [.1 in]**

Features

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Mechanical Attachment

Connector Mounting Type	Board Mount
Mating Alignment Type	Polarization
Mating Alignment	With
PCB Mount Retention	Without

Packaging Features

Packaging Method	Box
------------------	-----

Contact Features

Contact Base Material	Copper Alloy
PCB Contact Termination Area Plating Material	Tin
Contact Type	Socket
Contact Current Rating (Max)	1.5 A



Housing Features

Housing Material	Polyester - GF
Centerline (Pitch)	2.54 mm[.1 in]

Termination Features

Termination Method to PCB	Through Hole - Solder
Termination Post & Tail Length	3.3 mm[.13 in]

Product Type Features

Connector & Housing Type	Receptacle
Connector System	Board-to-Board
Connector & Contact Terminates To	Printed Circuit Board
DIN Size	Expanded
DIN Level	II

Configuration Features

Number of Positions	144
Number of Rows	3
PCB Mount Orientation	Vertical
Number of Columns	48
Rows Loaded	A, B, C
Number of Signal Positions	144

Dimensions

Row-to-Row Spacing	2.54 mm[.1 in]
--------------------	----------------

Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Signal
---------------------	--------

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------



EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 5148468-1  
ASSY,PIN,EUROCARD,TYPE C,LEAD-FREE,144/1


Customers Also Bought

TE Part #2-1318120-3  
DYNAMIC D2100 REC HSG 3P SGL Y

TE Part #173090-2  
.070 ECONOSEAL PLUG ASSY 2P

TE Part #350689-3  
UMNL SOK 24-18 PTPPHBZ L/P

TE Part #1-480763-0  
05P UMNL PLUG HSG NATL



TE Part #5111897-9  
[A/L UNIV HDR 40P ACT PIN SHT LAT](#)



TE Part #6-102567-0  
[70 MODII 2PC HDR DR SHRD .100, ROHS](#)




TE Part #6-532955-0  
[70 MODII 2PC CE RCPT ASSY, RoHS](#)



TE Part #2-382811-0  
[ECONOMY SHUNT, 30 AU BLACK](#)



TE Part #5-102567-6  
[50 MODII 2PC HDR DR SHRD .100, ROHS](#)



TE Part #1-1734101-7  
[Champ050 series, 50 pos,30u" Au, 3.30 H](#)

Documents

Product Drawings

[ASSY,RECPT,EUROCARD,TYPE C,L-FREE,144/15](#)

English

CAD Files

Customer View Model

[ENG\\_CVM\\_CVM\\_5148460-1\\_O.2d\\_dxf.zip](#)

English

3D PDF

3D

Customer View Model

[ENG\\_CVM\\_CVM\\_5148460-1\\_O.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_5148460-1\\_O.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Application Specification](#)

English

Agency Approvals

[UL](#)

English