




Z-PACK | Z-PACK 2mm HM

TE Internal #: 5100669-1
Hard Metric Backplane PCB Mount Header, ≤1 Gb/s, 25 Column, 7 Row, Mezzanine, 175 Position, 2 mm [.078 in] Centerline, Vertical, Gray, Z-PACK 2mm HM

[View on TE.com >](#)

Connectors > PCB Connectors > Backplane Connectors > Hard Metric Backplane Connectors >

Hard Metric Male Connector: Traditional Backplane, Mezzanine, 2mm



PCB Connector Assembly Type: **PCB Mount Header**

Data Rate: **≤1 Gb/s**

Number of Columns: **25**

Number of Rows: **7**

Backplane Architecture: **Mezzanine**

[All Hard Metric Male Connector: Traditional Backplane, Mezzanine, 2mm \(124\)](#)

Features

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Termination Features

Termination Method to PCB	Through Hole - Press-Fit
---------------------------	--------------------------

Mechanical Attachment

Connector Mounting Type	Board Mount
Front Mating Level	Level 1

Dimensions

Backplane Module Length	50 mm
-------------------------	-------

Operation/Application

Shielded	No
Circuit Application	Power & Signal



Contact Features

Contact Underplating Material	Nickel
Contact Base Material	Phosphor Bronze
CompactPCI Designation	None
PCB Contact Termination Area Plating Material	Tin
Feedthrough Post Length	3.7 mm
Contact Type	Pin
Contact Mating Area Plating Material	Gold
Contact Mating Area Plating Material Thickness	.5 µm[20 µin]
Contact Current Rating (Max)	1.5 A

Packaging Features

Packaging Quantity	10
Packaging Method	Tube

Housing Features

Housing Material	Polyester - GF
Centerline (Pitch)	2 mm[.078 in]

Configuration Features

Rows Loaded	Z, B, C, D, E, A, F
Number of Columns	25
Number of Rows	7
Backplane Architecture	Mezzanine
Number of Positions	175
PCB Mount Orientation	Vertical

Signal Characteristics

Crosstalk Version	Standard
Data Rate	≤1 Gb/s

Product Type Features

Connector & Contact Terminates To	Printed Circuit Board
Ground Feature Type	Ground Return Shielding
Backplane Interface Type	2mm HM
Connector System	Board-to-Board
PCB Connector Assembly Type	PCB Mount Header



Sealable	No
----------	----

Body Features

Primary Product Color	Gray
-----------------------	------

Usage Conditions

Operating Temperature Range	-55 – 125 °C[-67 – 257 °F]
-----------------------------	----------------------------

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance


For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 2391877-1
Z-PACK M.CONN.175P.EON



TE Part # CAT-472-Z12553
HM Receptacle Connector: Traditional Backplane, Coplanar, 2mm




TE Part # 434814-1
EXTR.TOOL SNGL.PIN




TE Part # 2170293-2
Z-PACK/B25 RAF 125P

Also in the Series | Z-PACK 2mm HM



Backplane Connector Housings(4)



Backplane Power Connectors(1)




Connector Caps & Covers(62)



Connector Contacts(2)



Insertion & Extraction Tools(2)




PCB Headers & Receptacles(46)



Power Contacts(2)

Customers Also Bought




TE Part #3-1761608-5
IDC LOW PRO HDR 50P VERT SHT L



TE Part #3-1879208-7
CPF 0402 330R 0.1% 25PPM 1K RL



TE Part #6-1879208-9
CPF 0402 6K8 0.1% 25PPM 1K RL



TE Part #254897-E
STVC 96 F ABC VV 7-00 TL 4,0 * 137 E007



TE Part #ZPF000000000007215
983-0RS 14-12 PN




TE Part #E80892-000
NSA937901E1



TE Part #104113-E
ERMB 125 FS 1 EE * 3,70 A-E V-V ** 247



TE Part #104114-E
ERMC 55 FS 1 EE * 3,70 A-E V-V * TRAY 24



Documents

Product Drawings

Z-PACK M.CONN.175P.

English

CAD Files

3D PDF

English

Customer View Model

ENG_CVM_5100669-1_C.2d_dxf.zip

English

Customer View Model

ENG_CVM_5100669-1_C.3d_igs.zip

English

Customer View Model

ENG_CVM_5100669-1_C.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English