




SFP56

TE Internal #: 2-2349201-2
zSFP+ Stacked (SFP56), Cage Assembly with Integrated Connector,
.6mm [.018in] Centerline, Signal

[View on TE.com >](#)

Connectors > Pluggable IO Connectors & Cages > SFP56 Stacked Cage Assembly: EMI Spring



Form Factor: **zSFP+ Stacked (SFP56)**
Pluggable I/O Product Type: **Cage Assembly with Integrated Connector**
Centerline (Pitch): **.6 mm [.018 in]**
Circuit Application: **Signal**
Operating Temperature Range: **-55 – 105 °C [-67 – 221 °F]**

[All SFP56 Stacked Cage Assembly: EMI Spring \(48\)](#)

Features

Termination Features

Termination Method to PCB	Through Hole - Press-Fit
---------------------------	--------------------------

Operation/Application

Pluggable I/O Applications	SFP28
Circuit Application	Signal

Product Type Features

Cage Type	Stacked
Form Factor	zSFP+ Stacked (SFP56)
Pluggable I/O Product Type	Cage Assembly with Integrated Connector

Configuration Features

Number of Positions	20
Number of Ports	24
Port Matrix Configuration	2 x 12

Electrical Characteristics



Data Rate (Max)	56 Gb/s
-----------------	---------

Housing Features

Centerline (Pitch)	.6 mm[.018 in]
--------------------	----------------

Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
-----------------------------	----------------------------

Other

Included Lightpipe	No
EMI Containment Feature Type	Internal/External EMI Springs
EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE’s information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) ‘Guidance on requirements for substances in articles’(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of ‘complex object’, the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA “Guidance on requirements for substances in articles” (June 2017, version 4.0) and will be updating its statements accordingly.



Compatible Parts

TE Part # 1761394-1
DUST COVER, SFP, GANGED & STACKED

Also in the Series | SFP56

Pluggable I/O Cable Assemblies(17)

Pluggable IO Connectors & Cages(53)

SFP, SFP+ & zSFP+(53)

Customers Also Bought

TE Part #6-2213362-2
RCPT ASSY,DIMMABLE PHOTOCONTROL,150C,3 P

TE Part #1734375-1
CHAMP .050 HIGH RISE, REVERSED

TE Part #2132529-3
IMP100S,H,V3P6C,LG,REW39,5.5

TE Part #5-1375870-4
RCPT ASSY,12 POS,VERT,0.8MM MI

TE Part #1-1871058-5
PCI EXPRESS CONN. EON TYPE, 280P, L=3.25

TE Part #1-2170287-1
1X4 CAGE ASSEMBLY, QSFP,SINGLE SQ LP

TE Part #1734100-3
Champ050 series,30pos,Au over PdNi

TE Part #1734101-3
Champ050 series,30pos,Au over PdNi



TE Part #1934949-1
Tinman 5pr 8col vert recpt 15mm stack



TE Part #2007808-2
IMP100S,H,V4P10C,LG,OEW46,4.9

Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2-2349201-2_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2-2349201-2_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2-2349201-2_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.