



Connectors > Automotive Connectors > Automotive Connector Accessories > Automotive Connector Caps & Covers



Protection & Strain Relief Accessory Type: **Shield Assembly**

Cable Exit Angle: **70°**

Strain Relief: **With**

Primary Product Color: **Black**

Primary Product Material: **Nylon GF**

Features

Packaging Features

Packaging Method	Package
Packaging Quantity	1

Other

Serviceable	No
EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Configuration Features

Compatible With Connector Code	C-F
Number of Positions	18

Product Type Features

Protection & Strain Relief Accessory Type	Shield Assembly
---	-----------------

Body Features

Cable Exit Angle	70°
Primary Product Color	Black
Primary Product Material	Nylon GF

Mechanical Attachment

Strain Relief	With
---------------	------



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 1326130-1
18WAY LAC LEVER

TE Part # 1326133-1
RECEPTACLE HOUSING, 18 POSITIO

Also in the Series | AMP 0.64 Connector System



Automotive Connector Caps & Covers (9)

Automotive Headers(5)

Automotive Housings(14)

Automotive Terminals(8)

Insertion & Extraction Tools(1)

PCB Headers & Receptacles(5)

Wire-to-Board Headers & Receptacles (5)

Customers Also Bought

TE Part #CAT-G3353-CH8172
GET .64 CONNECTOR SYSTEM, CONNECTOR HSG

TE Part #1924337-1
Shield Assembly, 54 POSN, 0.64mm BLK

TE Part #1924341-1
18P, 1 Row Carrier for54P LAC

TE Part #638551-2
CONTACT,FEMALE,0.64MM,SN,22

TE Part #327025
SPLICE,SOLIS BUTT STRAP 16-14

TE Part #2288274-2
24P HYBRID 0.64/2.8 PLUG ASSY, B KEY

TE Part #9-2208798-5
6POS,0.64 GENER. Y,REC HSG,ASSY

TE Part #2324930-1
REC CONN CVR ASSY,40POS,HYBRID

Documents

Product Drawings
18WAY LAC SHIELD ASSEMBLY 70 D

English

CAD Files
3D PDF
English
Customer View Model
ENG_CVM_1326132-1_A.2d_dxf.zip



English

Customer View Model

[ENG_CVM_1326132-1_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_1326132-1_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Instruction Sheets

[Instruction Sheet \(U.S.\)](#)

English