



Passive Components > Resistors > Surface Mount Resistors



Resistor Type: **Precision Resistor**

Element Type: **Thin Film**

Package Size Code: **0402**

Power Rating: **.063 W**

Resistance Value: **121K Ω**

Features

Industry Standards

Moisture Sensitivity Level	1
----------------------------	---

Usage Conditions

Operating Temperature Range	-55 – 155 °C
Temperature Coefficient	±25 ppm/°C

Product Type Features

Resistor Type	Precision Resistor
Element Type	Thin Film
Package Size Code	0402

Configuration Features

Number of Resistors	1
---------------------	---

Electrical Characteristics

Power Rating	.063 W
Resistance Value	121K Ω



Resistance Class	1kΩ – 1MΩ
Passive Component Tolerance	.1 %

Termination Features

Surface Mount Resistor Termination Type	Solder
Number of Terminations	2

Dimensions

Product Height	.3 mm[.012 in]
Product Length	1 mm[.039 in]
Product Width	.5 mm[.02 in]

Packaging Features

Packaging Method	Taped & Reeled
------------------	----------------

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits



as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 9-1879209-7
CPF 0402 121R 0.1% 25PPM 5K RL

TE Part # 2176280-8
CPF 0402 118K 0.1% 25PPM 1K RL

Also in the Series | Neohm CPF

Surface Mount Resistors(5842)

Customers Also Bought

TE Part #5-532955-5
30 MODII 2PC CE RCPT ASSY, RoHS

TE Part #2-2172067-2
M8 MALE R/A PNL.3P.PCB (AU)

TE Part #7-1625890-4
2W SM M/OX 5% 2K7

TE Part #2176349-2
CRGCO 2512 12R 1%

TE Part #1410189-1
MULTIGIG RT T2 7RW H-LFT,ET2

TE Part #254015-E
STVC 96 F ABC VVV 7-00 EE 5,5 * 137 E007

TE Part #254839-E
STVE 160 F ABCDE VVVV 7-00 EE 5,5 * 137

TE Part #484824-E
STVC 96 M ABC VVV 4-00 0606 * 8360 207 E



Documents

Product Drawings

CPF 0402 121K 0.1% 25PPM 1K RL

English

Datasheets & Catalog Pages

CPF-1016

English