




Terminals & Splices > Terminal Housings, Insulation Sleeves & Blocks > Crimp Terminal Housings



Terminal Type: **Receptacle**

Connector & Housing Type: **Receptacle**

Number of Positions: **2**

Terminal Orientation: **Straight**

UL Flammability Rating: **UL 94V-0**

Features

Dimensions

Product Length	24.38 mm[.96 in]
Product Height	8.28 mm[.326 in]

Packaging Features

Packaging Quantity	1
--------------------	---

Mechanical Attachment

Mating Alignment Type	Polarization
Mating Alignment	With
Connector Mounting Type	Cable Mount (Free-Hanging)

Body Features

Connector & Keying Code	C
Primary Product Color	Brown

Product Type Features

Sealable	No
Connector & Housing Type	Receptacle

Configuration Features



Number of Positions	2
---------------------	---

Contact Features

Terminal Type	Receptacle
Terminal Orientation	Straight
Contact Mating Retention	With

Housing Features

Housing Material	Nylon
Centerline (Pitch)	15.11 mm[.595 in]

Usage Conditions

Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]
-----------------------------	----------------------------

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products




will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Also in the Series | Positive Lock 250



Automotive Terminals(1)



Crimp Terminal Housings(184)



Insertion & Extraction Tools(3)




Insulation Boots & Sleeves(4)



Quick Disconnects(185)


Customers Also Bought



TE Part #7-87522-2
MOD IV RECP PLTD 30 DPLX LF



TE Part #2151582-1
OCEAN_2.0_Applicator-S-110F165O-RSM




TE Part #215882-6
AMP-LATCH MIL TYPE RCPT CONNECTOR



TE Part #2836077-1
OCEAN_2.0_Applicator-S-070F100O-RSM



TE Part #7-2150373-7
OCEAN-055F080F-CRIMPTOOLINGKIT




TE Part #7-2266813-7
OCEAN_2.0_SPARE_PART_KIT-055F062F



TE Part #7-2837932-7
OCEAN_2.0_SPARE_PART_KIT-062F091O



TE Part #926298-5
UN-MNL STECK-GEH 4P



Documents

Product Drawings

POSILOCK HSG,.250 SRS,MKIII,2P,V0,BR

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-521119-7_K.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1-521119-7_K.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1-521119-7_K.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English

Agency Approvals

UL Report

English