



Connectors > Terminal Blocks & Strips > Barrier Strips



Number of Positions: 2

Barrier Strip Style: **Tri-Barrier**

Bottom Termination Type: **Solderless Wire Wrap**

Connector System: **Wire-to-Board**

Centerline (Pitch): **9.53 mm [.375 in]**

Features

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features

Packaging Method	Package
Packaging Quantity	180

Operation/Application

Circuit Application	Power
---------------------	-------

Mechanical Attachment

Mounting Options	6-32 Mounting Threads
Screw Plating Material	Zinc
Screw Material	Steel
Thread Size	6-32
Connector Mounting Type	Panel Mount

Contact Features

--	--



Contact Base Material	Copper Alloy
PCB Contact Termination Area Plating Material	Tin
Contact Current Rating (Max)	25 A

Dimensions

Product Length	39.65 mm[1.561 in]
Wire Size	22 – 12 AWG

Housing Features

Housing Material	Thermoplastic
Centerline (Pitch)	9.53 mm[.375 in]

Product Type Features

Block Style	Flat Bottom with standoffs
Connector System	Wire-to-Board
Connector & Contact Terminates To	Wire & Cable

Body Features

Primary Product Color	Black
Product Orientation	Vertical
Barrier Strip Style	Tri-Barrier

Configuration Features

Number of Levels	1
Number of Positions	2
Number of Rows	1

Termination Features

Bottom Termination Type	Solderless Wire Wrap
-------------------------	----------------------

Electrical Characteristics

Operating Voltage	600 V, 300 V
-------------------	--------------

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------



EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 1-796988-4

6WWV-02-008=#6 TRIBARRIER TERM

Customers Also Bought

TE Part #1-6609027-5

10EK7=F7095 S0

TE Part #2267077-1

TMS1T4B5M2RE

TE Part #1658017-3

MSB0.80PL19ASY120FL,-,10,-TY

TE Part #2-1658012-3

MSB0.80RC-ASY120FL,-,10,-TY



TE Part #2176347-6
CRGCQ 2010 27R 1%

TE Part #9-1879352-1
RR02 5% 1K8 AMMO

TE Part #3-1462051-1
HF3 56S=50OHM140MW 12V MONO

TE Part #4-1879499-9
CRGH2010 5% 100R 1W

TE Part #3-1879280-1
RP 2A 178K 0.1% 15PPM CUT LENG

TE Part #1-292228-6
1.5 MINI CT SGL H SMT W/O BOSS

Documents

Product Drawings

6WWV-02-006=#6 TRIBARRIER

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_796608-2_K.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_796608-2_K.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_796608-2_K.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

BUCHANAN TERMINAL BLOCKS CATALOG - BARRIER STRIPS

English

1-1773458-2_BARRIER_STRIPS_QUICK_REFERENCE_GUIDE

English

Agency Approvals

UL

English

796608-2

2 Position Barrier Strip, Tri-Barrier, Solderless Wire Wrap Bottom Termination, Wire-to-Board, 9.53 mm [.375 in] Centerline, 1 Row, 300 V / 600 V

