

Sensors > Temperature Sensors > NTC Thermistors Sensors & Probes > NTC Thermistors



NTC Sensor Type: **NTC Thermistor**

Lead Wire Length: **65 mm [ 2.559 in ]**

Resistance (at 25°C): **10 kΩ**

Resistance Tolerance (at 25°C): **± 1 %**

Tolerance  $\beta$ -Value: **2 %**

## Features

### Product Type Features

NTC Sensor Type	NTC Thermistor
Resistance Tolerance (at 25°C)	± 1 %
Tolerance $\beta$ -Value	2 %

### Dimensions

Lead Wire Length	65 mm[2.559 in]
------------------	-----------------

### Usage Conditions

Resistance (at 25°C)	10 kΩ
Operating Temperature Range	-40 – 250 °C[-40 – 482 °F]

### Other

EU RoHS Compliance	Compliant with Exemptions
EU ELV Compliance	Compliant with Exemptions

### Product Compliance

For compliance documentation, visit the product page on [TE.com >](#)

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241)

Candidate List Declared Against: JUNE

2024 (241)

SVHC > Threshold:

Orange lead (60% in Component Part)

**Article Safe Usage Statements:**

Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

Halogen Content

Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free

Solder Process Capability

Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts



TE Part # GAG10K3976B1  
RSEN-GLASS BEAD

## Customers Also Bought



TE Part #GA10K3A1IA  
DISCRETE 10K OHMS, +/-0.1C FROM 0C TO 70C



TE Part #1630027-6  
HSC300 1R0 5%



TE Part #3-2176412-3  
5W XSM M/OX 5% 110R



TE Part #4-2176412-0  
5W XSM M/OX 5% 220R



## Documents

### Datasheets & Catalog Pages

[Radial\\_Glass\\_SeriesA\\_G10K3976](#)

English