




Terminals & Splices > Spade Terminals



Spade Terminal Type: **Spring Spade Terminal**
Wire Size: **5180 – 13100 CMA**
Stud Size: **#6, M3.5**

Features

Mechanical Attachment

Wire Insulation Support	With
-------------------------	------

Electrical Characteristics

Voltage Rating	600 V
----------------	-------

Industry Standards

Government Qualified Terminal	No
-------------------------------	----

Body Features

Insulation Sleeve Color	Yellow
Stripe Color	Yellow

Packaging Features

Packaging Quantity	500
Packaging Method	Loose Piece

Product Type Features

Stud Size	#6, M3.5
Sealable	No
Wire Insulation Support Retention Type	Insulation Support



Contact Features

Spade Terminal Type	Spring Spade Terminal
Barrel Type	Closed
Terminal Orientation	Straight
Terminal Plating Material	Tin

Dimensions

Wire Size	5180 – 13100 CMA
Stud Diameter	3.56 mm [.14 in]
Tongue Thickness	1.02 mm [.04 in]
Product Length	24.36 mm [.959 in]
Compatible Insulation Diameter (Max)	6.35 mm [.25 in]
Compatible Insulation Diameter Range	3.81 – 6.35 mm [.15 – .25 in]

Usage Conditions

Insulation Option	Partially Insulated
-------------------	---------------------

Operation/Application

Compatible With Wire Base Material	Copper
Compatible With Wire Plating Material	Tin

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>



EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability



Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts

 TE Part # 58423-1 DIE, RBY IS9252	 TE Part # 58433-3 PRO CR ASSY, RBY IS9252	 TE Part # 679300-1 1210 PIDG CRIMP HEAD	 TE Part # 539691-2 ERGO DIE R.B.Y
 TE Part # 169404 CERTI-LOK DIE	 TE Part # 2063030-1 SDE DIESET, RBY, UL	 TE Part # 59239-4 HHHT PIDG PG 12-10 ASSY	 TE Part # 59824-1 TETRA-CRIMP PIDG PG FASTON 22-10 ASSY
 TE Part # 47808-6 DIES PIDG 12-10 DIE SET	 TE Part # 169400 CERTI-LOK FRAME W/O DIES		

Also in the Series | PLASTI-GRIP




Compression Connectors(3)



Crimp Wire Pins, Tabs & Ferrules(20)



Ring Terminals(310)



Spade Terminals(159)




Splices(45)

Customers Also Bought




TE Part #SPD-12-3
STRING POT 12.5 INCH RANGE



TE Part #52420-1
TERMINAL,PIDG SPR SPD 16-14 6



TE Part #3-640429-3
03P MTA156 CONN ASSY 24AWG WHT




TE Part #1586024-5
5P S/R FH PLUG VAL-U-LOK V2



TE Part #3-643817-4
04P MTA156 CONN ASSY 18AWG ORA




TE Part #1445022-9
MICRO MNL RFCEPT HSG SINGLE R




TE Part #2029150-4
4P R/A HDR VAL-U-LOK V2 W/P



TE Part #640919-2
RECEPT,PIDG FASTON 16-14 187



TE Part #1586027-4
4P SR RCPT VAL-U-LOK V0



TE Part #5225059-3
SHV Jack Str Bulkhead Crimp RG-59, RG-62

Documents



Product Drawings

TERMINAL,PG SPR SPD 12-10 6

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_53246-1_K.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_53246-1_K.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_53246-1_K.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English

Agency Approvals

UL Report

English

UL Report

English