






REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A1	NEW DRAWING	23AUG2023	ASB	JDB
	E1	DRAWING RE-CREATED IN CREO	07DEC2023	NK	JDB
	E2	REEL CORE DIA CHANGE	24 JUL2024	SS	LET



TAPE ON REEL PACKAGING ACCORDING TO DIN IEC 60286-3
PACKAGING UNIT: 100 PCS



- DRAWING SPECIFICATION ACCORDING TO DOCUMENT 5_3_16-DOC-1806-00915
- COPLANARITY AREA OF TERMINATION ≤ 0,1MM/2



1	1	-	TAPE AND REEL	6
1	-	-	PAD	5
1	1	-	SOLDER CLIP LEFT	4
1	1	-	SOLDER CLIP RIGHT	3
6	6	-	PINS	2
1	1	-	M8 HOUSING	1
515814-E	464561-E	REV	DESCRIPTION	ITEM NO.
-	-	REV OF EACH ASSY NO. (WHEN BLANK, USE DWG. REV)		
QTY		PARTS LIST		

V= TURNED CONTACT (PCB SIDE CAN BE USED WITH POTTING COMPOUND)

- INSPECTION LEVEL 1: CONTROL CHART REQUIRED
① PROOF OF PROCESS CAPABILITY OR 100% TEST IF PROCESS CAPABILITY IS NOT ACHIEVED
- INSPECTION LEVEL 2 AND 3: CONTROL CHART REQUIRED
② PROOF OF MEAN VALUE STANDARD DEVIATION AND MACHINE CAPABILITY
- ③ PROOF OF VALUES OR PROOF OF ATTRIBUTIVE TEST
- INFORMATION ON THE SCOPE OF TESTING AND DETECTION BY ERNI VA 7.3.2.3

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN B. S. ADRUSH 21AUG2023	TE Connectivity		
DIMENSIONS: mm		CHK M. SZELAG 23AUG2023			
TOLERANCES UNLESS OTHERWISE SPECIFIED: DIM. FOR INFORMATION ISO 8015		APVD J. DE BRUIJN 23AUG2023	NAME M8 CIRCULAR CONNECTOR FEMALE CONNECTOR A CODE 6P 16.25 SMT V		
0 PLC 1 PLC 2 PLC 3 PLC 4 PLC ANGLES FINISH		PRODUCT SPEC 108-94887 APPLICATION SPEC 114-94781 WEIGHT -	SIZE A2	CAGE CODE 00779	DRAWING NO C=464561-E
MATERIAL -		CUSTOMER DRAWING	SCALE 5:1	SHEET 1 OF 1	REV E2