



Connectors > Connector Accessories > Connector Strain Relief



Strain Relief Accessory Type: Cable Clamp Kit

Primary Product Material: Polyester

Primary Product Color: Black

Compatible With Connector Shell Size: 13

Cable Entry Diameter: 9.14 mm [.36 in]

Features

Housing Features

Compatible With Connector Shape	Circular
Body Orientation	Right Angle

Product Type Features

Strain Relief Accessory Type	Cable Clamp Kit
------------------------------	-----------------

Body Features

Primary Product Material	Polyester
Primary Product Color	Black

Operation/Application

Compatible With Connector Shell Size	13
Shielded	No

Dimensions

Cable Entry Diameter	9.14 mm[.36 in]
----------------------	-----------------

Mechanical Attachment

Thread Size	3/4-20 UNEF-2B
-------------	----------------



Packaging Features

Packaging Method	Package
Packaging Quantity	1

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer





This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts





Also in the Series

AMP CPC



Customers Also Bought





Documents

Product Drawings

R/A STRN RELIEF KIT, SZ 13, CPC

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_213982-1_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_213982-1_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_213982-1_A.3d_stp.zip

English

3D PDF

English

Customer View Model

ENG_CVM_213982-1_O.2d_dxf.zip

English

Customer View Model

ENG_CVM_213982-1_O.3d_igs.zip

English

Customer View Model

ENG_CVM_213982-1_O.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English

Instruction Sheets

Instruction Sheet (U.S.)

English

213982-1

Cable Clamp Kit, Polyester, Black, Shell Size 13, 9.14 mm [.36 in] Cable Entry, AMP
CPC

