




Connectors > Terminal Blocks & Strips > PCB Terminal Blocks



Number of Positions: 4
Terminal Block Connector Type: Plug
Connector System: Wire-to-Board
Centerline (Pitch): 5.08 mm [.2 in]
Number of Rows: 1

Features

Termination Features

Termination Method to Wire & Cable	Push-in
------------------------------------	---------

Mechanical Attachment

Screw Plating Material	Nickel
Screw Material	Brass
Thread Size	M3

Body Features

Primary Product Color	Green
Product Orientation	Right Angle

Packaging Features

Packaging Method	Box
Packaging Quantity	200

Contact Features

Contact Mating Area Plating Material	Tin
--------------------------------------	-----



Contact Base Material	Phosphor Bronze
Contact Current Rating (Max)	15 A

Housing Features

Housing Material	PA 66
Centerline (Pitch)	5.08 mm[.2 in]

Product Type Features

Wire Protection	With
Terminal Block Connector Type	Plug
Connector System	Wire-to-Board
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Wire Entry Location	Side
Stacking Configuration	Side Stackable
Number of Positions	4
Number of Rows	1
Wire Entry Angle	180°

Electrical Characteristics

Operating Voltage	300 VAC
-------------------	---------

Dimensions

Wire Size	30 – 12 AWG
-----------	-------------

Usage Conditions

Operating Temperature Range	-40 – 110 °C[-40 – 230 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Other

EU RoHS Compliance	Compliant with Exemptions
EU ELV Compliance	Compliant with Exemptions

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions










China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2022 (224) SVHC > Threshold: Pb (2% in Component) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts


 TE Part # 282815-3 TERMI-BLOK HEADER,ASSY90 3P.5	 TE Part # 284061-3 TERMI-BLOK HDR 90, 5,08MM P. M	 TE Part # 284053-3 3P TERMI-BLOK HDR 90,5,08MM	 TE Part # 2342083-3 3POS HDR 90 DEG, HT,5.08MM PITCH,TL2.6MM
 TE Part # 284065-3 TERMI-BLOK HDR 180, 5.08MM P.M	 TE Part # 796636-3 3POS 5.08MM CE VRT HDR,TRM BLK	 TE Part # 796638-3 3POS 5.08MM CE R/A HDR,TRM BLK	 TE Part # 2342084-3 3POS HDR ST, HT, 5.08MM PITCH, TL 2.6MM



TE Part # 282814-3
[TERMI-BLOK HEADER,ASSY90 3P.5](#)




TE Part # 282824-3
[TERMI-BLOK HEADER,ASSY90 3P.5](#)



TE Part # 282825-3
[TERMI-BLOK HEADER,ASSY90 3P.5,](#)

Customers Also Bought




TE Part #5177983-6
[0.8FH,R05H.5,140,08/Sn,TU](#)




TE Part #7-215464-8
[08P.MICRO-MATCH MOB](#)




TE Part #8-1415537-0
[SR6B6K24](#)




TE Part #390111-1
[SKT,SODIMM,144P,SGRAM3.3V,HIGH, TY-S](#)



TE Part #5-106505-2
[9P.HDP20 REC.ASSY.](#)




TE Part #796638-3
[3POS 5.08MM CE R/A HDR,TRM BLK](#)



TE Part #2286211-3
[HIGH CURRENT SPRING FINGER](#)



TE Part #3-2176329-8
[CRGP 1210 12K 1%](#)



TE Part #166633-1
[IEC-F F.CONT.COSI](#)



TE Part #2-1617118-0
[J1MACD-26XM = M39016/23-030M](#)

Documents

Product Drawings

[TERMI-BLOK PLUG STACKING 3P.5,](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_282807-3_D.2d_dxf.zip](#)



English

Customer View Model

[ENG_CVM_CVM_282807-3_D.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_282807-3_D.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[BUCHANAN TERMINAL BLOCKS CATALOG - EUROSTYLE TERMINAL BLOCKS](#)

English

[BUCHANAN PCB TERMINAL BLOCKS](#)

English

[1-1773458-1_EURO_STYLE_TERMINAL_BLOCKS_QRG](#)

English

Product Specifications

[Application Specification](#)

English

Agency Approvals

[UL](#)

English