

T1210101116-000 ✓ ACTIVE

HDC | HDC IP65

TE Internal #: T1210101116-000


Heavy Duty Connector Hood, Side Entry, Locking, Sealable, HDC

IP65

[View on TE.com >](#)



Connectors > Rectangular Connectors > Rectangular Connector Hoods & Bases



Hood & Base Connector Product Type: **Hood**

Cable Entry Location: **Side**

Hood & Base Locking Device Type: **Locking**

Sealable: **Yes**

EU RoHS Compliance: **Compliant**

## Features

### Usage Conditions

Corrosion Protected	Yes
---------------------	-----

### Housing Features

Housing Material	Die Cast Aluminum
------------------	-------------------

### Packaging Features

Packaging Method	Box
------------------	-----

### Dimensions

Product Width	43 mm
---------------	-------

Product Length	73 mm
----------------	-------

### Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

### Mechanical Attachment

Thread Size	PG16
-------------	------

Locking Device Location	Hood
-------------------------	------

Hood & Base Locking Device Type	Locking
---------------------------------	---------

### Product Type Features

Hood & Base Connector Product Type	Hood
Sealable	Yes

### Body Features

Cable Entry Location	Side
----------------------	------

### Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

### Product Compliance

For compliance documentation, visit the product page on [TE.com](http://TE.com)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.
Solder Process Capability	Not reviewed for solder process capability

#### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


### Compatible Parts

TE Part # T2040102101-000  
HE-010-MTE Part # T1410102000-000  
H10B-AGTE Part # T3609160101-000  
DLX-16-MS

## Also in the Series | **HDC IP65**

Rectangular Connector Hoods & Bases  
(1257)

## Customers Also Bought

TE Part #440129-2  
2.0MM,HSG,2POSTE Part #2-2176231-9  
3522 150R 1% 3WTE Part #TAD14845101-020  
M12D4-MS-MR-PUR TYPE C GREEN-2.0MTE Part #1276716-1  
EXT-TOOL FOR DYNAMIC D2 CONNTE Part #234168-1  
EXTRACTION TOOL(DYNAMIC D-3)TE Part #1658622-6  
26 NOVO MIL/CTR 30DP,LEAD FREETE Part #1658622-1  
10 NOVO MIL/CTR 30DP,LEAD FREETE Part #2176416-1  
9W STD M/OX 5% 51RTE Part #T1210100116-000  
H10B-TS-PG16TE Part #1-1903328-4  
DYNAMIC 4200S HDR ASSY H 4P X

## Documents

### Product Drawings

[H10B-TS-PG16](#)

English

---

### CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG\\_CVM\\_CVM\\_T1210101116-000\\_A.2d\\_dxf.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_T1210101116-000\\_A.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_T1210101116-000\\_A.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

---

### Datasheets & Catalog Pages

[HEAVY DUTY CONNECTORS](#)

English

[HEAVY DUTY CONNECTORS](#)

Japanese

---

### Product Specifications

[Application Specification](#)

English