



Connectors > Power Connectors > Circular Power > Circular Power Connectors



Number of Positions: 7

Connector Product Type: **Housing**

Operating Voltage: **600 VDC**

Connector System: **Wire-to-Wire**

Sealable: **Yes**

Features

Packaging Features

| | |
|--------------------|---------|
| Packaging Quantity | 1 |
| Packaging Method | Package |

Mechanical Attachment

| | |
|--------------------------|----------------------------|
| Mating Retention Type | Threaded Coupling |
| Thread Size | 3/4 - 20 UNEF-2A |
| Polarization Code | A |
| Panel Mount Feature Type | Flange with Mounting Holes |
| Mating Alignment Type | Keyed |
| Mating Alignment | With |
| Connector Mounting Type | Panel Mount |
| Mating Retention | With |
| Panel Mount Feature | With |

Industry Standards

| | |
|---|-----|
| Compatible With Agency/Standards Products | VDE |
|---|-----|



| | |
|-----------------------------------|----------------------------|
| UL Flammability Rating | UL 94V-0 |
| Housing Features | |
| Body Orientation | Straight |
| Housing Color | Black |
| Housing Material | Nylon |
| Circular Connector Shell Size | 13 |
| Product Type Features | |
| Connector Seal & Plug Type | Peripheral |
| Connector Product Type | Housing |
| Connector System | Wire-to-Wire |
| Sealable | Yes |
| Connector & Contact Terminates To | Wire & Cable |
| Connector & Housing Type | Receptacle |
| Circular Connector Shell Type | All Plastic |
| Configuration Features | |
| Reverse Numbering | Without |
| Number of Positions | 7 |
| Number of Power Positions | 0 |
| Number of Signal Positions | 7 |
| Electrical Characteristics | |
| Operating Voltage | 600 VAC |
| Contact Features | |
| Reverse Gender | Yes |
| Contact Type | Socket |
| Contact Protection | With |
| Usage Conditions | |
| Operating Temperature Range | -55 – 105 °C[-67 – 221 °F] |
| Fluid Resistance | Immersion |
| Operation/Application | |
| Circuit Application | Power & Signal |
| Shielded | No |
| Other | |



| | |
|--------------------|-----------|
| EU RoHS Compliance | Compliant |
| EU ELV Compliance | Compliant |

Product Compliance

For compliance documentation, visit the product page on TE.com>

| | |
|---|---|
| EU RoHS Directive 2011/65/EU | Compliant |
| EU ELV Directive 2000/53/EC | Compliant |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold |
| EU REACH Regulation (EC) No. 1907/2006 | Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC |
| Halogen Content | BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources. |
| Solder Process Capability | Not applicable for solder process capability |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Also in the Series | AMP CPC



Connector Backshells(1)



Connector Caps & Covers(16)



Connector Contacts(6)



Connector Seals & Cavity Plugs(35)



Connector Strain Relief(60)



Insertion & Extraction Tools(1)



Power Contacts(6)

Customers Also Bought



TE Part #6609107-2
PS0SXDS60=C1027



TE Part #745253-3
20 DF SOCKET PLTD




TE Part #1-1879071-4
THS50 1R8 5%




TE Part #211102-1
CPC RECEPT ASSEMBLY SIZE 11-4



TE Part #211400-1
CPC PLUG ASSEMBLY SIZE 13-7




TE Part #163085-9
.062 DIA PIN ASS 3+




TE Part #163087-9
.062 SOC.ASS. TYP3+



TE Part #205841-3
CPC RECPT ASSEMBLY SIZE 11-8



TE Part #1-215297-5
15P HV100 REC CON. TE, 7.0MM



TE Part #160650-2
250 FASTON,PCB TAB,TNBR

Documents



CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_211398-3_AF.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_211398-3_AF.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_211398-3_AF.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English

Agency Approvals

UL Report

English