




NOTES:						
		A	RELEASED FOR PRODUCTION	07MAR2016	TX	SH
		A1	REVISED AS PER ECN-24-284280	13SEP2024	NR	ZW



THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±0.2
1 PLC ±0.2
2 PLC ±0.2
3 PLC ±0.2
4 PLC ±0.2
ANGLES ±3°
FINISH

1

2

DWN TIM XUE 13MAR2013
CHK ALEX CAI 13MAR2013
APVD ALEX CAI 13MAR2013
PRODUCT SPEC 108-51109
APPLICATION SPEC 114-60017
WEIGHT -
CUSTOMER DRAWING

NAME SAS-3 (12Gbps)SFF-8680 RECEPTACLE
DUAL PORT, WITH METAL RETENTION BLADE
HYBRID (TH/SMT) FOOTPRINT, 15P+7P+7P
SIZE A2
CAGE CODE 00779
DRAWING NO C-2170506
RESTRICTED TO -
SCALE 2:1
SHEET 1 OF 2
REV A1

TAPE & REEL WITH PICKUP CAP

2170506-1

PACKAGING

PART NUMBER

1471-9 (3/11)

