

VIP-2/PT/D15SUB/M - Termination board

2903779

<https://www.phoenixcontact.com/us/products/2903779>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

VARIOFACE module, with push-in connections and male D-SUB miniature pin strip, for mounting on NS 35 rails, 15-pos.



Commercial data

Item number	2903779
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	C423
Product key	CK2122
Catalog page	Page 554 (C-5-2019)
GTIN	4046356796545
Weight per piece (including packing)	91.4 g
Weight per piece (excluding packing)	91.4 g
Customs tariff number	85366990
Country of origin	US

VIP-2/PT/D15SUB/M - Termination board

2903779

<https://www.phoenixcontact.com/us/products/2903779>



Technical data

Product properties

Product type	Interface module
Product family	VARIOFACE Professional
Number of positions	15
No. of channels	15

Insulation characteristics

Overvoltage category	II
Pollution degree	2

Electrical properties

Nominal voltage U_N	25 V AC
	60 V DC
Max. current carrying capacity per branch	2 A
Rated surge voltage	1.2 kV

Connection data

Field level

Connection method	Push-in connection
Stripping length	8 mm
Conductor cross section rigid	0.14 mm ² ... 2.5 mm ²
Conductor cross section flexible	0.14 mm ² ... 2.5 mm ²
Conductor cross section AWG	26 ... 14

Controller level

Connection method	D-SUB pin strip
Number of connections	1
Number of positions	15

Signaling

Status display	no
Status display present	No

Dimensions

Item dimensions

Width	46.9 mm
Height	72.1 mm
Depth	63 mm

Material specifications

Color	gray (RAL 7042)
Housing insulation material	Polyamide PA non-reinforced

VIP-2/PT/D15SUB/M - Termination board

2903779

<https://www.phoenixcontact.com/us/products/2903779>



Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C

Standards and regulations

Standards/regulations	IEC 60664
	DIN EN 50178

Mounting

Mounting type	DIN rail mounting
Mounting position	any

Notes

Notes on operation	For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met.
--------------------	--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------

VIP-2/PT/D15SUB/M - Termination board


2903779

<https://www.phoenixcontact.com/us/products/2903779>



Drawings

Circuit diagram



VIP-2/PT/D15SUB/M - Termination board

2903779

<https://www.phoenixcontact.com/us/products/2903779>



Approvals

ⓘ To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2903779>

	CSA	Approval ID: 2122203		
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
	105 V	2 A	26 - 14	-

	cUL Recognized	Approval ID: E238705		
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
	125 V	2 A	26 - 14	-

	UL Recognized	Approval ID: E238705		
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
	125 V	2 A	26 - 14	-

	CSAus	Approval ID: 2122203		
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
	105 V	2 A	28 - 14	-

cULus Recognized

cCSAus

VIP-2/PT/D15SUB/M - Termination board

2903779

<https://www.phoenixcontact.com/us/products/2903779>



Classifications

ECLASS

ECLASS-11.0	27141152
ECLASS-12.0	27141152
ECLASS-13.0	27141152

ETIM

ETIM 9.0	EC002780
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

VIP-2/PT/D15SUB/M - Termination board

2903779

<https://www.phoenixcontact.com/us/products/2903779>



Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.	

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	445dc0cf-7ff5-44e1-a8e9-7fef81a6d8ac

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA

586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com