




Terminals & Splices > Quick Disconnects



Quick Disconnect Terminal Type: **Tab**

Wire Size: **.32 – .82 mm²**

Mating Tab Width: **4.75 mm [.187 in]**

Mating Tab Thickness: **.51 mm [.02 in]**

Features

Industry Standards

Compatible With Agency/Standards Products	UL, CSA
---	---------

Termination Features

Product Terminates To	Wire & Cable
-----------------------	--------------

Configuration Features

Compatible With Wire & Cable Type	Discrete Wire
Connection Capacity	Single

Mechanical Attachment

Wire Insulation Support	With
-------------------------	------

Packaging Features

Packaging Quantity	5000
Packaging Method	Strip/Reel

Dimensions

Product Length	17.14 mm[.675 in]
Compatible Insulation Diameter Range	2.03 – 3.05 mm[.08 – .12 in]



Terminal Material Thickness	.51 mm[.02 in]
Wire Size	.32 – .82 mm²

Product Type Features

Insertion Force	Low
-----------------	-----

Contact Features

Quick Disconnect Terminal Type	Tab
Mating Tab Width	4.75 mm[.187 in]
Mating Tab Thickness	.51 mm[.02 in]
Terminal Orientation	Straight
Contact Base Material	Brass
Terminal Plating Material	Tin
Crimp Type	F-Crimp
Barrel Type	Open

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	-40 – 110 °C[-40 – 230 °F]

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability



Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 1217118-1
110 FASTON,TAB,20-16 AWG,PTBR

TE Part # 1217891-1
187 FASTON,TAB,TPBR

TE Part # 2836284-2
OCEAN_2.0_Applicator-S-090F155O-RSA

TE Part # 7-2836284-7
OCEAN_2.0_SPARE_PART_KIT-090F155O

TE Part # 2836284-1
OCEAN_2.0_Applicator-S-090F155O-RSM

TE Part # 1742753-1
FASTON 2MM TAB 18-22AWG TPBR

TE Part # 2305570-1
Strip Terminal Cutter-Side Feed-No Crimp

Also in the Series | FASTON 187

Crimp Terminal Housings(41)

Insertion & Extraction Tools(1)

Joints & Splices(1)

PCB Terminals(42)



[Quick Disconnects\(207\)](#)



[Splices\(1\)](#)

Customers Also Bought




TE Part #1367645-6
[DWDM Kit Assy, Networking \(13.](#)



TE Part #1879075-8
[THS25 R39 5%](#)



TE Part #60598-3
[058PIN REC IS 22-20 010PTPPHBZ](#)




TE Part #62192-1
[BOBBIN TAB .016TPBR](#)




TE Part #184030-1
[RECPT, CONTACT 070, AUPHBZ](#)



TE Part #42710-2
[205 FASTON REC 22-18 AWG TPBR](#)



TE Part #776127-2
[2POS .070 MULTILOCK PLUG RIGHT](#)



TE Part #1612904-2
[025 24POS CAP ASSY V TIN](#)



TE Part #2-1977223-4
[FSM8JSMASSTR=6MM TACT SWITCH, SMT 160gf,](#)



TE Part #E818213001
[ASC99555BCK0066](#)

Documents

Product Drawings

[187 FASTON TAB 22-18 AWG TPBR](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_42490-3_AT.2d_dxf.zip](#)



English

Customer View Model

[ENG_CVM_CVM_42490-3_AT.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_42490-3_AT.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[FASTON Tabs](#)

English

Product Specifications

[Application Specification](#)

English

Agency Approvals

[UL Report](#)

English