




EMI & EMC Solutions > EMI Filters > Power Line Filters > Single Phase Filters > Single Phase Filters, Corcom HT Series



Current Rating: **6 A**

Input Termination Type: **Wire Lead**

Output Termination Type: **Wire Lead**

Leakage Current (Max) (120VAC, 60Hz): **.002 mA**

Leakage Current (Max) (250VAC, 50Hz): **.005 mA**

[All Single Phase Filters, Corcom HT Series \(9\)](#)

Features

Mechanical Attachment

Panel Mount Feature Type	Flange
--------------------------	--------

Usage Conditions

Operating Temperature Range	-10 – 40 °C
-----------------------------	-------------

Product Type Features

Filtering Requirements	Filtered
Ground Choke Option	No
Input Termination Type	Wire Lead
Output Termination Type	Wire Lead

Electrical Characteristics

Current Rating	6 A
Leakage Current (Max) (120VAC, 60Hz)	.002 mA
Leakage Current (Max) (250VAC, 50Hz)	.005 mA
Operating Voltage	250 VAC



Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CAT-C8114-H857  
Single Phase Filters, Corcom HQ Series




TE Part # CAT-C8114-H85999  
Single Phase Filters, Corcom HT Series

Also in the Series | Corcom HT




Single Phase Filters(9)

Customers Also Bought



TE Part #3-643814-3  
03P MTA100 CONN ASSY POL RIB



TE Part #640456-6  
06P MTA100 HDR ASSY F/L SQ STR



TE Part #1939708-1  
Industrial Ethernet Cat5e (AWG



TE Part #5205817-1  
KIT SCREWLOCK FEMALE



TE Part #1-66741-1  
TYPE XII FEMALE CONT (STRIP)



TE Part #1735801-1  
2.0mm,Crimp,Contact



TE Part #1-794226-0  
MINI UMN2 PIN 26-22AWG LP LF



TE Part #208485-1  
CMC RECPT ASSEMBLY SIZE 28



TE Part #1879026-4  
YR1 0.1% 10R



TE Part #NB14614001  
VERSAFIT-3/8-9-SP

Documents

Product Drawings

6EHT3=F7665 S0

English

CAD Files

Customer View Model

ENG\_CVM\_CVM\_6609053-6\_A1.3d\_igs.zip

English

Customer View Model



[ENG\\_CVM\\_CVM\\_6609053-6\\_A1.3d\\_stp.zip](#)

English

**Customer View Model**

[ENG\\_CVM\\_CVM\\_6609053-6\\_A1.2d\\_dxf.zip](#)

English

**3D PDF**

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

**Datasheets & Catalog Pages**

[1654001\\_CORCOM\\_PRODUCT\\_GUIDE\\_HT\\_SERIES](#)

English

**Corcom Combined Selector Charts**

English

[1-1654250-1\\_CORCOM\\_EMI\\_RFI\\_QRG](#)

English